

## QLINE D PUSHBUTTON ENCLOSURE TYPE 4X



Used for insulating and housing 30.5-mm or 22.5-mm pushbuttons in hostile environments, QLine D Enclosures have contoured bodies with flush cover screws for an attractive, contemporary appearance.

### FEATURES & BENEFITS

---

High-impact polycarbonate material is used for both body and cover

Polycarbonate material is easily punched, drilled, filed or sawed

Straight side walls permit ganging of multiple enclosures

Cross-point captivated cover screws are stainless steel

Mounting holes molded directly adjacent to cover screws

Cover screws protected by removable caps that are both aesthetic and provide tamper resistance

Molded internal pads for mounting optional panels, rails or other components

Seamless foam-in-place gasket assures watertight and dust-tight seal

Screws provided for mounting optional panel

Optional panels are unpainted plated steel

Mounting hardware furnished

Material is halogen free

### SPECIFICATIONS

---

**Finish** Smooth Gloss

**Color** Light Gray

**Color Code** RAL 7035

**Hole Size** 22.5 mm

Table 1/2

Catalog Number	Height	Width	Depth	Protection Rating	Material	Thickness
Q1PBPCDM	75 mm	73 mm	79 mm	NEMA Type 12; NEMA Type 13; NEMA Type 4; NEMA Type 4X; IP66	Polycarbonate	3 mm
Q2PBPCDM	113 mm	73 mm	79 mm	NEMA Type 12; NEMA Type 13; NEMA Type 4; NEMA Type 4X; IP66	Polycarbonate	3.5 mm
Q3PBPCDM	153 mm	73 mm	79 mm	NEMA Type 12; NEMA Type 13; NEMA Type 4; NEMA Type 4X; IP66	Polycarbonate	3 mm
Q4PBPCDM	193 mm	113 mm	79 mm	NEMA Type 12; NEMA Type 13; NEMA Type 4; NEMA Type 4X; IP66	Polycarbonate	3 mm

Table 2/2

Catalog Number	External Dimensions	Panel	Panel Size	Mounting
Q1PBPCDM	82 x 80 mm	Q88PD	68 x 55 mm	70 x 50 mm
Q2PBPCDM	120 x 80 mm	Q128PD	131 x 65 mm	108 x 50 mm
Q3PBPCDM	160 x 80 mm	Q168PD	170 x 100 mm	148 x 50 mm
Q4PBPCDM	200 x 120 mm	Q2012PD	170 x 100 mm	188 x 90 mm

**Finish** Smooth Gloss

**Color** Light Gray

**Color Code** RAL 7035

**Hole Size** 22.5 mm

Table 1/2

Catalog Number	Height	Width	Depth	Protection Rating	Material	Thickness
Q1PBPCDM	75 mm	73 mm	79 mm	NEMA Type 12; NEMA Type 13; NEMA Type 4; NEMA Type 4X; IP66	Polycarbonate	3 mm
Q2PBPCDM	113 mm	73 mm	79 mm	NEMA Type 12; NEMA Type 13; NEMA Type 4; NEMA Type 4X; IP66	Polycarbonate	3.5 mm
Q3PBPCDM	153 mm	73 mm	79 mm	NEMA Type 12; NEMA Type 13; NEMA Type 4; NEMA Type 4X; IP66	Polycarbonate	3 mm
Q4PBPCDM	193 mm	113 mm	79 mm	NEMA Type 12; NEMA Type 13; NEMA Type 4; NEMA Type 4X; IP66	Polycarbonate	3 mm

Table 2/2

Catalog Number	External Dimensions	Panel	Panel Size	Mounting
Q1PBPCDM	82 x 80 mm	Q88PD	68 x 55 mm	70 x 50 mm

Catalog Number	External Dimensions	Panel	Panel Size	Mounting
Q2PBPCDM	120 x 80 mm	Q128PD	131 x 65 mm	108 x 50 mm
Q3PBPCDM	160 x 80 mm	Q168PD	170 x 100 mm	148 x 50 mm
Q4PBPCDM	200 x 120 mm	Q2012PD	170 x 100 mm	188 x 90 mm

Purchase panels separately

2100 Hoffman Way  
 Anoka, MN 55303-1745 | USA  
 763.421.2240



Our powerful portfolio of brands:  
[nVent.com](https://www.nVent.com) **CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2023 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.