

## SCREW COVER CONTOURED TYPE 4

With its aesthetic, rounded corners, this enclosure is an economical solution for a broad range of electrical and terminal wiring applications that do not require a back panel.



### FEATURES & BENEFITS

No welded seams or sharp corners

Formed flanged cover

Cover screws

Oil-resistant gasket

External welded-on mounting brackets for easy installation.

Bonding provision on cover

Grounding Stud on body

### SPECIFICATIONS

**Color** Gray

**Color Code** ANSI 61

**Finish** Powder Coated

Table 1/2

Catalog Number	Height	Width	Depth	Protection Rating	Material	Mounting
----------------	--------	-------	-------	-------------------	----------	----------

A402DSC	102 mm	51 mm	51 mm	NEMA Type 12; NEMA Type 4; IP67	Mild Steel	114 mm
A404DSC	102 mm	102 mm	67 mm	NEMA Type 12; NEMA Type 4; IP67	Mild Steel	127 mm
A403DSC	114 mm	73 mm	67 mm	NEMA Type 12; NEMA Type 4; IP67	Mild Steel	127 mm

Table 2/2

Catalog Number	Overall Dimensions	Thickness
A402DSC	129 x 62 mm	1.52 mm
A404DSC	140 x 113 mm	1.52 mm
A403DSC	141 x 84 mm	1.52 mm

2100 Hoffman Way  
 Anoka, MN 55303-1745 | USA  
 763.421.2240



Our powerful portfolio of brands:  
 nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2022 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.  
 nVent reserves the right to change specifications without notice.