

## FIBERGLASS DISCONNECT TYPE 4X



For effective and economical disconnect protection in the harshest corrosive environments, these enclosures provide secure door closure through the use of Type 304 stainless steel slotted quarter-turn latches. Each Fiberglass Disconnect, Type 4X is furnished with bracket affixed to door for attaching disconnect door catch (interlock) and instructions for installing disconnect handle (handle not included).

### FEATURES & BENEFITS

---

Fiberglass-reinforced material has excellent temperature and chemical resistance qualities and exhibits outstanding physical properties

Seams are sealed; no holes or knockouts

Seamless foam-in-place gasket assures water-tight and dust-tight seal

Fiberglass material is easily drilled, filed or sawed

Hinges are fiberglass reinforced polyester

Doors are secured with Type 304 stainless steel slotted quarter-turn latches

Data pocket is high-impact thermoplastic

Copper flashed steel collar studs for mounting optional panels and terminal block kits

Holes provided in body for mounting disconnect operating handle and operating mechanism; disconnect operating handle not included

Internal grounding provisions for quarter-turn latches

### SPECIFICATIONS

---

**Protection Rating** NEMA Type 4X; IP66

**Material** Fiberglass

**Finish** Smooth Matte

**Color** Light Gray

**Color Code** RAL 7035

**Thickness** 3 mm

Table 1/2

Catalog Number	Height	Width	Depth	Panel Size	Conductive Panel	Mounting
A20HS1610GQRLP	513 mm	413 mm	254 mm	432 x 330 mm	A20P16G	554 x 254 mm
A24HS2412GQRLP	614 mm	614 mm	305 mm	533 x 533 mm	A24P24G	656 x 457 mm
A24HS2408GQRLP	614 mm	614 mm	203 mm	533 x 533 mm	A24P24G	656 x 457 mm
A24HS2008GQRLP	616 mm	514 mm	203 mm	533 x 432 mm	A24P20G	657 x 356 mm
A30HS2412GQRLP	768 mm	616 mm	305 mm	686 x 533 mm	A30P24G	812 x 457 mm
A36HS3012GQRLP	921 mm	768 mm	305 mm	838 x 686 mm	A36P30G	955 x 610 mm
A48HS3612GQRLP	1226 mm	921 mm	305 mm	1143 x 838 mm	A48P36G	1259 x 762 mm
A60HS3612GQRLP	1530 mm	922 mm	305 mm	1448 x 838 mm	A60P36G	1564 x 762 mm

Table 2/2

Catalog Number	Panel	Latch Quantity
A20HS1610GQRLP	A20P16	2
A24HS2412GQRLP	A24P24	2
A24HS2408GQRLP	A24P24	2
A24HS2008GQRLP	A24P20	2
A30HS2412GQRLP	A30P24	2
A36HS3012GQRLP	A36P30	4
A48HS3612GQRLP	A48P36	5
A60HS3612GQRLP	A60P36	5

Purchase panels separately

Optional stainless steel, composite and aluminum panels available for most sizes. See General Accessories.

No additional "C" dimensions available

2100 Hoffman Way  
Anoka, MN 55303-1745 | USA  
763.421.2240



Our powerful portfolio of brands:  
[nVent.com](https://www.nVent.com) **CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2023 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.