

SEQUESTR HIGH-AMP EXTERNAL DISCONNECT TYPE 4 AND 12



Isolate high-amp disconnect switches and breakers in the Sequestr external disconnect enclosure to mitigate arc flash incidents. Install on free-stand or floor-mount disconnect enclosures to reduce exposure to incoming power. When the disconnect handle is turned OFF, there is no live power on the load side cables passing through to the main enclosure. The Sequestr enclosure is sized for use with up to 800A cable operated disconnect switches or breakers dependent on NEC 430.10(B), and is designed to fit with bulletins A34, A35, A28, A21 and A4L3D main enclosures. Refer to installation manual for configuration mounting and hole pattern.

FEATURES & BENEFITS

Seams continuously welded and ground smooth

Interlocks with doors of main enclosure when the disconnect handle is powered ON to prevent opening when energized

Disconnect handle mounts on main enclosure

Designed to house cable-operated disconnect switches or breakers for mounting flexibility

Maintains UL Type rating of main enclosure

Quarter-turn, slotted 3-point latch installed; padlocking handle shipped loose to provide additional level of security

Conductive back panel included

Hinged on right side

Removable door with hidden hinges for clean, aesthetic appearance

Bonding provision on door

Mounting and interlocking hardware included

SPECIFICATIONS

Thickness 1.9 mm

Finish Powder Coated

Color Gray

Color Code ANSI 61

Table 1/1

Catalog Number	Height	Width	Depth	Protection Rating	Material
AXD542018C	1372 mm	508 mm	457 mm	NEMA Type 4; NEMA Type 12; NEMA Type 3R; IP66	Mild Steel
AXD542024C	1372 mm	508 mm	613 mm	NEMA Type 4; NEMA Type 12; NEMA Type 3R; IP66	Mild Steel

2100 Hoffman Way
Anoka, MN 55303-1745 | USA
763.421.2240



Our powerful portfolio of brands:
[nVent.com](https://www.nvent.com) **CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2022 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.
nVent reserves the right to change specifications without notice.