

**DOOR STOP KIT**



**APPLICATION**

Designed for use on most standard nVent HOFFMAN Type 4 and 12 enclosures to secure the door in an open position. Enclosures must have a "B" dimension of 16.00 in. (406 mm) or more and a door which opens horizontally. Door Stop Kit is not intended for use on Concept window door enclosures, or enclosures configured with a swing-out panel or swing-out rack frame. Door stop kit is not intended for use in high-wind conditions.

**FEATURES**

- Can be mounted at the top or bottom of the door opening
- The angle of the door is easily adjusted by means of a wingnut
- The stop arm slides neatly out of the way when the door is closed
- Maintains UL/CSA Type 4, 4X, and 12 if properly installed in an nVent HOFFMAN enclosure

**SPECIFICATIONS**

- All parts are plated mild steel
- Includes stainless steel mounting screws and nylon washers

**BULLETIN: A80**

Catalog Number	Description
ADSTOPK	Door Stop Kit

**DOOR STOP KIT, WALL-MOUNT ENCLOSURES**



**APPLICATION**

Designed for use with most standard wall-mount enclosures to secure the door in an open position. This door stop kit is ideal for use in applications that require the kind of corrosion protection that only Type 316 stainless steel can provide. Typical applications include water treatment, pulp, paper, petroleum, chemical, food and pharmaceutical processing, and packaging. Door stop kit is not intended for use in high-wind conditions.

**FEATURES**

- Can be mounted at either top or bottom of door
- Can be installed on either left- or right-hinged doors
- Maintains UL/CSA Type 4, 4X, and 12 if properly installed in an nVent HOFFMAN enclosure

**SPECIFICATIONS**

- All parts are Type 316 stainless steel
- Includes stainless steel mounting screws and nylon washers

**BULLETIN: A4SY**

Catalog Number	Description
ADSTOPKSS6	Door Stop Kit, Wall-Mount Enclosures

**DOOR STOP KIT, LARGE ENCLOSURES**



**APPLICATION**

Designed for use with most standard, free-stand or floor-mount enclosures to secure the door in a 90-degree open position. This door stop kit is not intended for use in high-wind conditions.

**FEATURES**

- Can be mounted at the top or bottom of the door opening after drilling two small holes in the door and the enclosure
- Maintains UL/CSA Type 4, 4X, and 12 if properly installed in an nVent HOFFMAN enclosure

**SPECIFICATIONS**

- All parts are plated mild steel
- Includes stainless steel mounting screws and nylon washers

**BULLETIN: A80**

Catalog Number	Description
ALGDSTOP2	Door Stop Kit, Large Enclosures

**DOOR STOP KIT, FREE-STAND OR FLOOR-MOUNT ENCLOSURES**



**APPLICATION**

Designed for use with most standard, free-stand and floor-mount enclosures to secure the door in a minimum of 90-degree open position. It can be used in a variety of outside plant environments and applications and is designed to meet Telcordia GR-487-CORE vertical door restrainer requirements for wind loading conditions. This door stop kit is ideal for use in applications that require the kind of corrosion protection that only Type 316 stainless steel can provide. It is not intended for use in free-stand or floor-mount enclosures with quarter-turn latches; the quarter-turn latches will interfere with the door stop bracket when installed.

**FEATURES**

- Designed to be mounted at the bottom of door
- Can be installed on either left- or right-hinged doors
- Maintains UL/CSA Type 4, 4X, and 12 if properly installed in an nVent HOFFMAN enclosure

**SPECIFICATIONS**

- All parts are Type 316 stainless steel
- Includes stainless steel seal screws and hardware

**BULLETIN: A4SY**

Catalog Number	Description
ALGDSTOPKSS6	Door Stop Kit, Free-Stand or Floor-Mount Enclosures