

TYPE 4 FREE-STANDING ENCLOSURES ACCESSORY SELECTION

(See Accessories for Details)

Panels

Steel	Conductive	Description	Panel Size	Single-Door Single-Access Enclosures		Single-Door Dual Access Enclosures			
				A72H2518FS	A72H3124FS	A72G374FS	A72H2518FS3PT	A72H3124FS3PT	A72H3724FS3PT
A60P24F1	A60P24F1G	Full Panel	48.00 x 20.00 (1219 x 508)	• ^a			• ^a		
A60P24F2	A60P24F2G	Half Panel	24.88 x 20.00 (632 x 508)	• ^a			• ^a		
A72P24F1	A72P24F1G	Full Panel	60.00 x 20.00 (1524 x 508)	•			•		
A72P24F2	A72P24F2G	Half Panel	30.88 x 20.00 (784 x 508)	•			•		
A90P24F2	A90P24F2G	Half Panel	39.00 x 20.00 (1013 x 508)	• ^a			• ^a		
A72P30F1	A72P30F1G	Full Panel	60.00 x 26.00 (1524 x 660)		•			•	
A72P30F2	A72P30F2G	Half Panel	30.88 x 26.00 (784 x 660)		•			•	
A60P36F1	A60P36F1G	Full Panel	48.00 x 32.00 (1219 x 813)			• ^a			• ^a
A60P36F2	A60P36F2G	Half Panel	24.88 x 32.00 (632 x 813)			• ^a			• ^a
A72P36F1	A72P36F1G	Full Panel	60.00 x 32.00 (1524 x 813)			•			•
A72P36F2	A72P36F2G	Half Panel	30.88 x 32.00 (784 x 813)			•			•
A90P36F2	A90P36F2G	Half Panel	39.88 x 32.00 (1013 x 813)			• ^a			• ^a

Swing-Out Panels

Catalog No.	Description	Panel Size	Single-Door Single-Access Enclosures		Single-Door Dual Access Enclosures		
A72SP24F3	Full Panel	60.00 x 18.81 (1524 x 478)	•			•	
A72SP24F4	Half Panel	30.88 x 18.81 (784 x 478)	•			•	
A72SP30F3	Full Panel	60.00 x 24.81 (1524 x 630)		•			•
A72SP30F4	Half Panel	30.88 x 24.81 (784 x 630)		•			•
A72SP36F3	Full Panel	60.00 x 30.81 (1524 x 783)			•		•
A72SP36F4	Half Panel	30.88 x 30.81 (784 x 783)			•		•

Side-Mount Panels

Catalog No.	Description	Panel Size	Single-Door Single-Access Enclosures		Single-Door Dual Access Enclosures		
A72SMP14	Side-Mount Panel	60.00x14.00 (1524x356)	•			•	•
A72SMP20	Side-Mount Panel	60.00x20.00 (1524x508)	•			•	•

Heavy-Duty Panel Supports

Catalog No.	Description	Length	Single-Door Single-Access Enclosures		Single-Door Dual Access Enclosures		
A72FSHDPS	Two Full-Length Panel Supports	60.25 (1759)	•			•	•

Clamp Nuts

Catalog No.	Description	For	Single-Door Single-Access Enclosures		Single-Door Dual Access Enclosures		
APS1420CN	1/4-20 Clamp Nut (Qty. 20)	Special Use	•			•	•
APS51618CN	5/16-18 Clamp Nut (Qty. 20)	Special Use	•			•	•

Clip Nut Packages*

Catalog No.	Description	Size	Fits	Single-Door Single-Access Enclosures		Single-Door Dual Access Enclosures		
AN1032	Plated (Qty. 20)	#10-32	"RA" Type Rack Mount Angles	•			•	
ANM5	Plated (Qty. 20)	Metric M5	"RA" Type Rack Mount Angles		•			•

Casters

Catalog No.	Description	Size	Single-Door Single-Access Enclosures		Single-Door Dual Access Enclosures		
DMCKC	Set of 4 Casters	4 high x 3 diameter	•			•	•

Rack-Mount Angles L-Style (Type RP) for 19- and 24-in. Equipment

Catalog No.	Description	For Rack Size	Angle Length	Number of Rack Units	Single-Door Single-Access Enclosures		Single-Door Dual Access Enclosures		
A60RP24F5	Two Full-Length Angles	19.00 (483)	49.00 (1245)	28	•			•	
A72RP24F5	Two Full-Length Angles	19.00 (483)	61.25 (1556)	35	•			•	
A72RP24F6	Two Full-Length Angles	19.00 (483)	31.50 (800)	18	•			•	
A72RP30F5	Two Full-Length Angles	24.00 (610)	61.25 (1556)	35		•			•
A72RP30F6	Two Full-Length Angles	24.00 (610)	31.50 (800)	18		•			•
A90RP24F5	Two Full-Length Angles	24.00 (610)	40.25 (1022)	23	•			•	

Rack-Mount Angles U-Style (Type RA) for 19- and 24-in. Equipment

Catalog No.	Description	For Rack Size	Angle Length	Number of Rack Units	Single-Door Single-Access Enclosures		Single-Door Dual Access Enclosures		
A60RA19TH	Two Full-Length Angles	19.00 (483)	49.00 (1245)	28	•			•	
A72RA19TH	Two Full-Length Angles	19.00 (483)	61.25 (1556)	35	•			•	
A72RA24TH	Two Full-Length Angles	24.00 (610)	61.25 (1556)	35		•			•

Millimeter dimensions are in parentheses ()

One rack unit = 1.75 in. (45 mm)

^a Requires heavy-duty panel supports

^b Requires swing-out rack mounting frame

* Requires rack angles

Notes