

Declaration of Conformity

Issued by Manufacturer Hoffman Enclosures, Inc.
2100 Hoffman Way, Anoka, Minnesota 55303-1745, U.S.A.

declare at our sole responsibility, that these devices are designed and constructed according to
the fundamental safety and health requirements.

Enclosure Models: KBA - - -, EBU - - - (bulletin HLY)

Equipment Description: Hoffman Cable Fittings for Use in Zone Classified Locations

Equipment Certification: UL and cUL Recognized Component per construction detailed below

Applicable Standards: UL 2225 Standard for Cables and Cable-Fittings For Use In Hazardous
(Classified) Locations
cUL C22.2 No.60079 Explosive Atmospheres
IEC/EN 60079 Standards for Explosive Atmospheres

Authorized by:



2/18/2022

Tom Hurney

Date

Technology Mgr., Product Compliance and Approvals



Cable Fittings for Use in Zone Classified Hazardous Locations

[See General Information for Cable Fittings for Use in Zone Classified Hazardous Locations](#)

BIMED TEKNIK ALETLER SAN TIC A S

E474828

BEYLIKDUZU MEVKII

SS BAKIR VE PIRINC SAN

ORKIDE CD NO 15

34524 ISTANBUL, BEYLIKDUZU TURKEY

Class I, Zone 1, AEx e IIC, cable fittings, for use only with TC-ER-HL cable, thread sizes 1/2 to 1 in. NPT or M20 to M32, "Series Orion Lower Temperature (Orion LT)", Model(s) KBA, followed by 1 thru 3, may be followed by X, followed by M or N, followed by LT, followed by B, BN, X, followed by C or S, may be followed by -WC or -WS.

Class I, Zone 1, AEx e IIC, cable fittings, for use only with TC-ER-HL cable, thread sizes 1/2 to 1-1/2 in. NPT or M20 to M50, "Series Orion", Model(s) KBA, followed by 1 thru 5, may be followed by S, XS, XM or L, followed by M or N, followed by B, BN, X or A, followed by C or S, may be followed by -WC or -WS.

Class I, Zone 1, AEx e IIC, cable fittings, for use only with TC-ER-HL cable, thread sizes 1/2 to 1-1/2 in. NPT or M20 to M50, "Series Orion Universal", Model(s) KBAU, followed by numerals 1 thru 5, may be followed by S, XS, XM or L, followed by M or N, followed by B, BN, X or A, followed by C or S, may be followed by -WC or -WS.

Class I, Zone 1, AEx e IIC, cable fittings, for use only with TC-ER-HL cable, thread sizes 1/2 to 1-1/4 in. NPT or M20 to M4, "Series Vela", Model(s) EBS followed by 1 thru 4, followed by M or N, followed by B, BN, X or A, followed by C or S, followed by -WC or -WS

Class I, Zone 1, AEx e IIC, cable fittings, for use only with TC-ER-HL cable, thread sizes 1/2 to 1-1/4 in. NPT or M20 to M40, "Series Octans", Model(s) EBU, followed by 1 thru 4, 12, 23 or 34, followed by M or N, followed by B, BN, X or A, followed by C or S.

Class I, Zone 1, AEx e IIC, cable fittings, for use only with TC-ER-HL cable, thread sizes 1/2 to 1-1/4 in. NPT or M20 to M40, "Series Taurus", Model(s) KBAT, followed by 1 thru 5, may be followed by S or L, followed by M or N, followed by B, BN, X or A, followed by C or S, may be followed by -WC or -WS.

Class I, Zone 2, AEx e IIC, cable fittings, for use only with TC and TC-ER and TC-ER-HL cable, thread sizes 1/2 to 3 in. NPT or M20 to M90, "Series Vela", Model(s) EBS followed by 1 thru 12, followed by M or N, followed by B, BN, X or A, followed by C or S, followed by -WC or -WS (

Class I, Zone 2, AEx e IIC, cable fittings, for use only with TC and TC-ER and TC-ER-HL cable, thread sizes 1/2 to 4 in. NPT or M20 to M110, "Series Octans", Model(s) EBU, followed by 1 thru 12, 23, 34, 45, 56, 67, 78 or 810, followed by M or N, followed by B, BN, X or A, followed by C or S.

Class I, Zone 2, AEx e IIC, cable fittings, for use only with TC, TC-ER and TC-ER-HL cable, thread sizes 1/2 to 1 in. NPT or M20 to M32, "Series Orion Lower Temperature (Orion LT)", Model(s) KBA, followed by 1 thru 3, may be followed by X, followed by M or N, followed by LT, followed by B, BN, X, followed by C or S, may be followed by -WC or -WS.

Class I, Zone 2, AEx e IIC, cable fittings, for use only with TC, TC-ER and TC-ER-HL cable, thread sizes 1/2 to 2 in. NPT or M20 to M63, "Series Taurus", Model(s) KBAT, followed by 1 thru 6, may be followed by S or L, followed by M or N, followed by B, BN, X or A, followed by C or S, may be followed by -WC or -WS.

Class I, Zone 2, AEx e IIC, cable fittings, for use only with TC, TC-ER and TC-ER-HL cable, thread sizes 1/2 to 3-1/2 in. NPT or M20 to M110, "Series Orion", Model(s) KBA, followed by 1 thru 10, may be followed by S, XS, XM or L, followed by M or N, followed by B, BN, X or A, followed by C or S, may be followed by -WC or -WS.

Class I, Zone 2, AEx e IIC, cable fittings, for use only with TC, TC-ER and TC-ER-HL cable, thread sizes 1/2 to 3-1/2 in. NPT or M20 to M110, "Series Orion Universal", Model(s) KBAU, followed by 1 thru 10, may be followed by S, XS, XM or L, followed by M or N, followed by B, BN, X or A, followed by C or S, may be followed by -WC or -WS.

Zone 21, Ex tb IIIC Db, cable fittings, for use only with TC-ER-HL cable, thread sizes 1/2 to 1 in. NPT or M20 to M32, "Series Octans", Model(s) EBU, followed by 1 thru 4, 12, 23 or 34, followed by M or N, followed by B, BN, X or A, followed by C or S.

Zone 21, Ex tb IIIC Db, cable fittings, for use only with TC-ER-HL cable, thread sizes 1/2 to 1 in. NPT or M20 to M32, "Series Vela", Model(s) EBS followed by 1 thru 12, followed by M or N, followed by B, BN, X or A, followed by C or S, followed by - WC or - WS

Zone 22, AEx tc IIIC, cable fittings, for use only with TC and TC-ER and TC-ER-HL cable, thread sizes 1/2 to 3 in. NPT or M20 to M90, "Series Vela", Model(s) EBS followed by 1 thru 12, followed by M or N, followed by B, BN, X or A, followed by C or S, followed by -WC or -WS

Zone 22, AEx tc IIIC, cable fittings, for use only with TC and TC-ER and TC-ER-HL cable, thread sizes 1/2 to 4 in. NPT or M20 to M110, "Series Octans", Model(s) EBU, followed by 1 thru 12, 23, 34, 45, 56, 67, 78 or 810, followed by M or N, followed by B, BN, X or A, followed by C or S.

Zone 22, AEx tc IIIC, cable fittings, for use only with TC, TC-ER and TC-ER-HL cable, thread sizes 1/2 to 1 in. NPT or M20 to M32, "Series Orion Lower Temperature (Orion LT)", Model(s) KBA, followed by 1 thru 3, may be followed by X, followed by M or N, followed by LT, followed by B, BN, X, followed by C or S, may be followed by -WC or -WS.

Zone 22, AEx tc IIIC, cable fittings, for use only with TC, TC-ER and TC-ER-HL cable, thread sizes 1/2 to 2 in. NPT or M20 to M63, "Series Taurus", Model(s) KBAT, followed by 1 thru 6, may be followed by S or L, followed by M or N, followed by B, BN, X or A, followed by C or S, may be followed by -WC or -WS.

Zone 22, AEx tc IIIC, cable fittings, for use only with TC, TC-ER and TC-ER-HL cable, thread sizes 1/2 to 3-1/2 in. NPT or M20 to M110, "Series Orion", Model(s) KBA, followed by 1 thru 10, may be followed by S, XS, XM or L, followed by M or N, followed by B, BN, X or A, followed by C or S, may be followed by -WC or -WS.

Zone 22, AEx tc IIIC, cable fittings, for use only with TC, TC-ER and TC-ER-HL cable, thread sizes 1/2 to 3-1/2 in. NPT or M20 to M110, "Series Orion Universal", Model(s) KBAU, followed by 1 thru 10, may be followed by S, XS, XM or L, followed by M or N, followed by B, BN, X or A, followed by C or S, may be followed by -WC or -WS.

Trademark and/or Tradename: "BIMED" , 

Last Updated on 2019-03-13

BIMED TEKNİK ALETLER SAN TIC A S
BEYLIKDUZU MEVKII
SS BAKIR VE PIRINC SAN
ORKIDE CD NO 15

ISTANBUL, 34524 Turkey

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2020 UL LLC"



Cable Fittings for Use in Zone Classified Hazardous Locations Certified for Canada

[See General Information for Cable Fittings for Use in Zone Classified Hazardous Locations Certified for Canada](#)

BIMED TEKNIK ALETLER SAN TIC A S

E474828

BEYLIKDUZU MEVKII

SS BAKIR VE PIRINC SAN

ORKIDE CD NO 15

34524 ISTANBUL, BEYLIKDUZU TURKEY

Class I, Zone 1, Ex e IIC, cable fittings, for use only with TC-ER-HL cable, thread sizes 1/2 to 1-1/4 in. NPT or M20 to M40, "Series Vela", Model(s) EBS followed by 1 thru 4, followed by M or N, followed by B, BN, X or A, followed by C or S, followed by -WC or -WS

Class I, Zone 2, Ex e IIC, cable fittings, for use only with TC and TC-ER and TC-ER-HL cable, thread sizes 1/2 to 3 in. NPT or M20 to M90, "Series Vela", Model(s) EBS followed by 1 thru 12, followed by M or N, followed by B, BN, X or A, followed by C or S, followed by -WC or -WS

Class I, Zone 1, Ex e IIC Gb, cable fittings, for use only with TC-ER-HL cable, thread sizes 1/2 to 1 in. NPT or M20 to M32, "Series Orion Lower Temperature, "Series Orion Lower Temperature (Orion LT)", Model(s) KBA, followed by 1 thru 3, may be followed by X, followed by M or N, followed by LT, followed by B, BN, X, followed by C or S, may be followed by -WC or -WS.

Class I, Zone 1, Ex e IIC Gb, cable fittings, for use only with TC-ER-HL cable, thread sizes 1/2 to 1-1/2 in. NPT or M20 to M50, "Series Orion", Model(s) KBA, followed by 1 thru 5, may be followed by S, XS, XM or L, followed by M or N, followed by B, BN, X or A, followed by C or S, may be followed by -WC or -WS.

Class I, Zone 1, Ex e IIC Gb, cable fittings, for use only with TC-ER-HL cable, thread sizes 1/2 to 1-1/2 in. NPT or M20 to M50, "Series Orion Universal", Model(s) KBAU, followed by 1 thru 5, may be followed by S, XS, XM or L, followed by M or N, followed by B, BN, X or A, followed by C or S, may be followed by -WC or -WS.

Class I, Zone 1, Ex e IIC Gb, cable fittings, for use only with TC-ER-HL cable, thread sizes 1/2 to 1-1/4 in. NPT or M20 to M40, "Series Octans", Model(s) EBU, followed by 1 thru 4, 12, 23 or 34, followed by M or N, followed by B, BN, X or A, followed by C or S.

Class I, Zone 1, Ex e IIC Gb, cable fittings, for use only with TC-ER-HL cable, thread sizes 1/2 to 1-1/4 in. NPT or M20 to M40,, "Series Taurus", Model(s) KBAT, followed by 1 thru 5, may be followed by S or L, followed by M or N, followed by B, BN, X or A, followed by C or S, may be followed by -WC or -WS.

Class I, Zone 2, Ex e IIC Gc, cable fittings, for use only with TC and TC-ER and TC-ER-HL cable, thread sizes 1/2 to 4 in. NPT or M20 to M110, "Series Octans", Model(s) EBU, followed by 1 thru 12, 23, 34, 45, 56, 67, 78 or 810, followed by M or N, followed by B, BN, X or A, followed by C or S.

Class I, Zone 2, Ex e IIC Gc, cable fittings, for use only with TC, TC-ER and TC-ER-HL cable, thread sizes 1/2 to 1 in. NPT or M20 to M32,, "Series Orion Lower Temperature (Orion LT)", Model(s) KBA, followed by 1 thru 3, may be followed by X, followed by M or N, followed by LT, followed by B, BN, X, followed by C or S, may be followed by -WC or -WS.

Class I, Zone 2, Ex e IIC Gc, cable fittings, for use only with TC, TC-ER and TC-ER-HL cable, thread sizes 1/2 to 2 in. NPT or M20 to M63, "Series Taurus", Model(s) KBAT, followed by 1 thru 6, may be followed by S or L, followed by M or N, followed by B, BN, X or A, followed by C or S, may be followed by -WC or -WS.

Class I, Zone 2, Ex e IIC Gc, cable fittings, for use only with TC, TC-ER and TC-ER-HL cable, thread sizes 1/2 to 3-1/2 in. NPT or M20 to M110, "Series Orion", Model(s) KBA, followed by 1 thru 10, may be followed by S, XS, XM or L, followed by M or N, followed by B, BN, X or A, followed by C or S, may be followed by -WC or -WS.

Class I, Zone 2, Ex e IIC Gc, cable fittings, for use only with TC, TC-ER and TC-ER-HL cable, thread sizes 1/2 to 3-1/2 in. NPT or M20 to M110, "Series Orion Universal", Model(s) KBAU, followed by 1 thru 10, may be followed by S, XS, XM or L, followed by M or N, followed by B, BN, X or A, followed by C or S, may be followed by -WC or -WS.

Zone 21, Ex tb IIIC Db, cable fittings, for use only with TC-ER-HL cable, thread sizes 1/2 to 1 in. NPT or M20 to M32, "Series Octans", Model(s) EBU, followed by 1 thru 4, 12, 23 or 34, followed by M or N, followed by B, BN, X or A, followed by C or S.

Zone 21, Ex tb IIIC Db, cable fittings, for use only with TC-ER-HL cable, thread sizes 1/2 to 1 in. NPT or M20 to M32, "Series Orion Lower Temperature (Orion LT)", Model(s) KBA, followed by 1 thru 3, may be followed by X, followed by M or N, followed by LT, followed by B, BN, X, followed by C or S, may be followed by -WC or -WS.

Zone 21, Ex tb IIIC Db, cable fittings, for use only with TC-ER-HL cable, thread sizes 1/2 to 1 in. NPT or M20 to M32, "Series Vela", Model(s) EBS followed by 1 thru 12, followed by M or N, followed by B, BN, X or A, followed by C or S, followed by -WC or -WS

Zone 21, Ex tb IIIC Db, cable fittings, for use only with TC-ER-HL cable, thread sizes 1/2 to 1-1/2 in. NPT or M20 to M50, "Series Orion", Model(s) KBA, followed by 1 thru 5, may be followed by S, XS, XM or L, followed by M or N, followed by B, BN, X or A, followed by C or S, may be followed by -WC or -WS.

Zone 21, Ex tb IIIC Db, cable fittings, for use only with TC-ER-HL cable, thread sizes 1/2 to 1-1/2 in. NPT or M20 to M50, "Series Orion Universal", Model(s) KBAU, followed by 1 thru 5, may be followed by S, XS, XM or L, followed by M or N, followed by B, BN, X or A, followed by C or S, may be followed by -WC or -WS.

Zone 21, Ex tb IIIC Db, cable fittings, for use only with TC-ER-HL cable, thread sizes 1/2 to 1-1/4 in. NPT or M20 to M40, "Series Octans", Model(s) EBU, followed by 1 thru 4, 12, 23 or 34, followed by M or N, followed by B, BN, X or A, followed by C or S.

Zone 21, Ex tb IIIC Db, cable fittings, for use only with TC-ER-HL cable, thread sizes 1/2 to 1-1/4 in. NPT or M20 to M40, "Series Taurus", Model(s) KBAT, followed by 1 thru 5, may be followed by S or L, followed by M or N, followed by B, BN, X or A, followed by C or S, may be followed by -WC or -WS.

Zone 22, Ex tc IIIB Dc, cable fittings, for use only with TC and TC-ER and TC-ER-HL cable, thread sizes 1/2 to 4 in. NPT or M20 to M110, "Series Octans", Model(s) EBU, followed by 1 thru 12, 23, 34, 45, 56, 67, 78 or 810, followed by M or N, followed by B, BN, X or A, followed by C or S.


Zone 22, Ex tc IIIB Dc, cable fittings, for use only with TC, TC-ER and TC-ER-HL cable, thread sizes 1/2 to 1 in. NPT or M20 to M32, "Series Orion Lower Temperature (Orion LT)", Model(s) KBA, followed by 1 thru 3, may be followed by X, followed by M or N, followed by LT, followed by B, BN, X, followed by C or S, may be followed by -WC or -WS.

Zone 22, Ex tc IIIB Dc, cable fittings, for use only with TC, TC-ER and TC-ER-HL cable, thread sizes 1/2 to 2 in. NPT or M20 to M63, "Series Taurus", Model(s) KBAT, followed by 1 thru 6, may be followed by S or L, followed by M or N, followed by B, BN, X or A, followed by C or S, may be followed by -WC or -WS.

Zone 22, Ex tc IIIB Dc, cable fittings, for use only with TC, TC-ER and TC-ER-HL cable, thread sizes 1/2 to 3-1/2 in. NPT or M20 to M110, "Series Orion", Model(s) KBA, followed by 1 thru 10, may be followed by S, XS, XM or L, followed by M or N, followed by B, BN, X or A, followed by C or S, may be followed by -WC or -WS.

Zone 22, Ex tc IIIB Dc, cable fittings, for use only with TC, TC-ER and TC-ER-HL cable, thread sizes 1/2 to 3-1/2 in. NPT or M20 to M110, "Series Orion Universal", Model(s) KBAU, followed by 1 thru 10, may be followed by S, XS, XM or L, followed by M or N, followed by B, BN, X or A, followed by C or S, may be followed by -WC or -WS.

Zone 22, Ex tc IIIC, cable fittings, for use only with TC and TC-ER and TC-ER-HL cable, thread sizes 1/2 to 3 in. NPT or M20 to M90, "Series Vela", Model(s) EBS followed by 1 thru 12, followed by M or N, followed by B, BN, X or A, followed by C or S, followed by -WC or -WS

Trademark and/or Tradename: "BIMED" , 

[Last Updated](#) on 2019-03-13

BIMED TEKNİK ALETLER SAN TIC A S
BEYLIKDUZU MEVKII
SS BAKIR VE PIRINC SAN
ORKIDE CD NO 15
ISTANBUL, 34524 Turkey

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2020 UL LLC"