

# DNG-IEC\_NA

Glazed doors | Floor Standing Enclosures



**Description:** Glazed door with fitted clear safety glass to view the inside of the enclosure. Equipped with double-bit 3 mm lock system and door frame. Allows all options of the locking program. Compatible with combinable and compact enclosure ranges.

**Material:** Frame: 2 mm steel plate. Viewing area: 4 mm clear safety glass.

**Finish:** RAL 7035 structured powder coating.

**Protection:** Complies with IP 55 | TYPE 12 | IK 07.

**Pack quantity:** 1 piece.

**Mounting requirements:** Use hinge kit DNMK01 if no door was fitted previously.

For enclosure		
H	W	Item no.
1800	600	DNG1806R5
1800	800	DNG1808R5
2000	600	DNG2006R5
2000	800	DNG2008R5
2000	1000	DNG2010R5
2200	600	DNG2206R5
2200	800	DNG2208R5