



HOFFMAN ENCLOSURES, INC.  
2100 Hoffman Way  
Minneapolis, MN 55303-1745, USA  
+1.763.421.2240 main

# Declaration of Conformity

Issued by Manufacturer  
Hoffman Enclosures, Inc.  
2100 Hoffman Way, Anoka, Minnesota 55303-1745, U.S.A.  
declare at our sole responsibility, that these devices are designed and constructed according to  
the fundamental safety and health requirements.

Enclosure Models: APWK\*\*\*\*H (Bulletin A80W)  
Equipment Description: Hoffman Type 12 Hinged Window Kits  
Enclosure Rating: CSA Type 12  
Enclosure Certification: CSA C22.2 No. 14 - 13

## PRODUCTS

CLASS 3211 07 - INDUSTRIAL CONTROL EQUIPMENT-Miscellaneous Apparatus  
CLASS 3211 87 - INDUSTRIAL CONTROL EQUIPMENT-Miscellaneous Apparatus - Certified to US Standards

Hinged window kits, Series A-PWKXXXXXH, CSA Type 12, max size 30 in by 24 in.  
Permanently mounted window kits, Series A-PWKXXXXXNF, CSA Types 4, 12, max size 37.5 in by 25.5 in,  
Series A-PWKXXXXXNFSS, Type 4X, 4, 12, max size 31.5 in by 21.5 in.

Applicable Standards: CSA C22.2 No. 14 - 13 – Industrial Control Equipment  
CAN/CSA C22.2 No. 94-M91 – Special Purpose Enclosures  
ANSI/UL 50 (11<sup>th</sup> edition) – Enclosures for Electrical Equipment  
ANSI/UL 508 (13<sup>th</sup> edition) – Industrial Control Equipment

Authorized by: Glen Kampa 5/22/2020 (today's date)

**Glen Kampa** **Date**

Senior Regulatory Engineer

Subject to Change Without Notice

DOC: CERT-00257-B



# Certificate of Compliance

Certificate: 70076407 Master Contract: 151630 (042186\_C\_000)  
Project: 70177560 Date Issued: 2018-04-12  
Issued to: Hoffman Enclosures Inc.  
2100 Hoffman Way  
Anoka, Minnesota 55303-1745  
USA  
Attention: Glen Kampa

*The products listed below are eligible to bear the CSA Mark shown with adjacent indicators 'C' and 'US' for Canada and US or with adjacent indicator 'US' for US only or without either indicator for Canada only.*



Issued by: Douglas Bramwell  
Douglas Bramwell

## PRODUCTS

CLASS 3211 07 - INDUSTRIAL CONTROL EQUIPMENT-Miscellaneous Apparatus  
CLASS 3211 87 - INDUSTRIAL CONTROL EQUIPMENT-Miscellaneous Apparatus - Certified to US Standards

Hinged window kits, Series A-PWKXXXXXH, CSA Type 12, max size 30 in by 24 in.  
Permanently mounted window kits, Series A-PWKXXXXXNF, CSA Types 4, 12, max size 37.5 in by 25.5 in,  
Series A-PWKXXXXXNFSS, Type 4X, 4, 12, max size 31.5 in by 21.5 in.

### Notes:

1. For use only in Certified equipment where the acceptability of the combination is determined by Canadian Standards Association.
2. These devices are for mounting in enclosures having the same type environmental ratings.
3. Window kits, Series A-PWK53XXXXXNF and A-PWKXXXXXH may be provided with acrylic (Acrylite) (in lieu of polycarbonate Lexan) window, if shock hazard does not exist behind the observation opening.
4. 4."XXXXX" is catalogue designation denotes dimensions.



**Certificate:** 70076407

**Project:** 70177560

**Master Contract:** 151630

**Date Issued:** 2018-04-12

---

**APPLICABLE REQUIREMENTS**

CSA C22.2 No. 14-13	-Industrial Control Equipment
CAN/CSA-C22.2 No. 94-M91	-Special Purpose Enclosures
UL Std No.508, 17 <sup>th</sup> Ed	-Industrial Control Equipment
UL Std No. 50, 13 <sup>TH</sup> Ed	-Enclosures for Electrical Equipment