



CONNECT AND PROTECT

Express Customization

Days matter. We ship within 10.



Days matter. We ship within 10.

When you need customized enclosures quickly, nVent HOFFMAN gives you the choice—fast or faster.

Need something fast? **Factory Express** lets you choose from a broad selection of our most common enclosures, add 2D holes and cutouts, and pick a paint color. Shipped from our factory within 10 days.*

Need something faster? With **Local Express**, available through our network of distributor-operated Modification Centers, you choose an off-the-shelf enclosure, add 2D holes and cutouts, and receive your enclosure in a few days.

Express Customization from nVent HOFFMAN helps you get it done.

Local Express: Holes/Cutouts within Days

With Local Express, you get the holes and cutouts you need within days. Contact your local distributor for more details.



**Fastest option for quick-turn,
low-volume projects**



**Modified at a local distributor
from off-the-shelf inventory**



**Expertly made 2D holes and cutouts
with precision equipment**



**Delivered within days, contact your
local modification center***

*actual delivery times may vary based on location, distributor inventory, or other unforeseen circumstances. No guarantees or warranties are offered in this document. For our complete terms and conditions, please see <https://www.nvent.com/terms/hoffman-na.html>



Factory Express: Holes/Cutouts + Paint in 10 days

Factory Express allows you to modify our most popular enclosures with 2D holes and cutouts and add paint - all shipped in 10 days.

1

Select from more than 1,500 of our most popular enclosure and panel models

2

Add 2D holes and cutouts where you need them

3

Choose your paint from a 28-color palette, including OSHA safety colors

Models and colors subject to change.









1







Select your product

Select from more than 1,500 of our most commonly ordered panels, wall-mount, free-stand and floor-mount enclosures.

Like all nVent HOFFMAN products, Factory Express-eligible panels and enclosures are designed to meet global safety standards and perform under the most challenging conditions. Available in mild or stainless steel. Gain peace of mind knowing you're protecting your investment with the industry's best enclosures.

WALL-MOUNT ENCLOSURES










	CONTINUOUS HINGE			WATERSHED		DISCONNECT		
Product	Single Door with Clamps 	Single Door with 3-Point Latch 	Two Door 	Single Door 	Disconnect 	Preferred Cutout Disconnect 	Disconnect with Clamps 	Allen-Bradley 1494 Cutout 
Bulletin	A12 A4 A4S	A4W3 A4SW3	A12 A4SW	WS1	WS1D	A25	A19 A19S	A22
Size Range	12 x 24 to 60 x 36	16 x 12 to 72 x 36	24 x 42 to 42 x 60	16 x 12 to 60 x 36	24 x 25 to 60 x 37	20 x 22 to 60 x 38	24 x 21 to 60 x 37	24 x 22 to 60 x 38
Type Rating	Mild Steel: Type 4, 12, 13 Stainless Steel: Type 3R, 4, 4X, 12	Mild Steel: Type 4, 12, 13 Stainless Steel: Type 3R, 4, 4X, 12	Mild Steel: Type 12 Stainless Steel: Type 3R, 4, 4X, 12	Type 4, 4X, 12	Type 4, 4X, 12	Type 12, 13	Mild Steel: Type 4, 12, 13 Stainless Steel: Type 3R, 4, 4X, 12	Type 12, 13

	CONCEPT					
Product	Single Door 	Window Door 	Flush Mount 	Two Door 	Sloped Top 	Disconnect 
Bulletin	CW1 CWS	CW1 CWS	CW1	CW1	CW2	CWD CWSD
Size Range	12 x 10 to 60 x 36	12 x 10 to 48 x 24	12 x 12 to 30 x 24	24 x 42 to 48 x 48	12 x 12 to 36 x 30	20 x 22 to 30 x 26
Type Rating	Mild Steel: Type 4, 12, 13 Stainless Steel: Type 3R, 4, 4X, 12	Mild Steel: Type 4, 12, 13 Stainless Steel: Type 3R, 4, 4X, 12	Type 4, 12, 13	Type 12	Type 4, 12, 13	Mild Steel: Type 4, 12, 13 Stainless Steel: Type 3R, 4, 4X, 12





Models and colors subject to change.

FREE-STAND & FLOOR-MOUNT ENCLOSURES

	FREE-STAND		FLOOR-MOUNT	
Product	Single and Dual Access 	Single Door 	Two Door 	Two Door with 3-Point Latches 
Bulletin	A30 A30S4	A4L3 A4SL	A12L A4SL	A4L3 A4S3
Size Range	60 x 24 to 90 x 72	72 x 25 to 72 x 37	54 x 42 to 72 x 72	42 x 48 to 74 x 72
Type Rating	Mild Steel: Type 12 Stainless Steel: Type 3R, 4, 4X, 12	Mild Steel: Type 4, 12 Stainless Steel: Type 3R, 4, 4X, 12	Mild Steel: Type 12 Stainless Steel: Type 3R, 4, 4X, 12	Mild Steel: Type 4, 12 Stainless Steel: Type 3R, 4, 4X, 12

	GENERAL PURPOSE				WATERSHED		DISCONNECT		
Product	Single Door Free-Stand 	Single Door Free-Stand Disconnect 	Two Door Floor-Mount 	Two Door Floor-Mount Disconnect 	Free-Stand 	Free-Stand Disconnect 	Heavy-Duty Free-Stand Disconnect 	Universal Free-Stand 	Two Door Floor-Mount Disconnect 
Bulletin	A4S2	A4S2	A4S2	A4S2	WS2	WS2D	A28M1 A28M2 A28S4	A35	A21 A21S4
Size Range	72 x 24 to 72 x 36	72 x 27 to 72 x 39	60 x 48 to 72 x 72	60 x 49 to 72 x 73	62 x 51 to 74 x 63	62 x 51 to 74 x 63	72 x 28 to 90 x 78	72 x 40 to 84 x 78	60 x 49 to 72 x 72
Type Rating	Type 3R, 4, 4X, 12	Type 3R, 4, 4X, 12	Type 3R, 4, 4X, 12	Type 3R, 4, 4X, 12	Type 4, 4X, 12	Type 4, 4X, 12	Mild Steel: Type 12 Stainless Steel: Type 3R, 4, 4X, 12	Mild Steel: Type 3R, 4, 12 Stainless Steel: Type 3R, 4, 4X, 12	Mild Steel: Type 12 Stainless Steel: Type 3R, 4, 4X, 12

PANELS

Product	Concept Panels 	Panels for Type 3R, 4, 4X, 12 and 13 Enclosures 	Panels for Free-Stand Enclosures with Mounting Channel 	Panels for Free-Stand Enclosures with Mounting Stud 
Bulletin	CWP	PNLWM	PNL30	PNLFS
Size Range	12 x 10 to 72 x 36	12 x 24 to 72 x 72	60 x 24 to 90 x 36	72 x 28 to 90 x 78

2

Add holes and cutouts

Design your product with 2D holes and cutouts, placed where you need them to fit your application's needs.

Whether to run conduit, wiring or add products into your enclosures—simple customization* is no problem with Factory Express. Precision cutting assures your enclosure fits exactly as designed so you don't need to modify on the fly.



* Enclosures and panels requiring forming, knockouts or additional customization are not eligible for Express Customization. In addition, high quantity orders may require split shipments. If all of the order cannot be shipped within 10 days, nVent HOFFMAN will work with you on a schedule that best fits your production needs.

3

Choose your color

Choose from a vibrant palette of 28 colors. Smooth and rough gloss and semi-gloss textures available.

Note: painted stainless steel products are not included in the Express Customization program.

Standard Colors



ANSI 61 HOFFMAN Standard Gray
Smooth Semi Gloss



RAL 7035 Light Gray
Rough Textured Semi Gloss



HOFFMAN White
Smooth Semi Gloss

Other Colors



RAL 3005 Wine Red
Rough Textured Gloss



RAL 3001 Signal Red
Smooth Gloss



OSHA Safety Red
Rough Textured Gloss



RAL 2002 Vermillion
Rough Textured Gloss



RAL 2004 Pure Orange
Smooth Gloss



OSHA Safety Orange
Rough Textured Gloss



RAL 2000 Yellow Orange
Smooth Gloss



RAL 1023 Traffic Yellow
Smooth Gloss



OSHA Safety Yellow
Rough Textured Gloss



RAL 6011 Reseda Green
Smooth Gloss



RAL 6003 Olive Green
Smooth Gloss



OSHA Safety Blue
Rough Textured Gloss




RAL 5002 Ultramarine Blue
Rough Textured Gloss



RAL 5005 Signal Blue
Smooth Gloss



RAL 5015 Sky Blue
Rough Textured Gloss



RAL 9010 Pure White
Smooth Gloss



RAL 9001 Cream
Smooth Gloss



RAL 1013 Oyster White
Smooth Gloss



RAL 1015 Light Ivory
Smooth Gloss



RAL 9002 Gray White
Smooth Gloss




RAL 7035 Light Gray
Smooth Gloss



RAL 7038 Agate Gray
Smooth Gloss



RAL 7032 Pebble Gray
Smooth Gloss



RAL 9003 Signal White
Smooth Gloss



RAL 9005 Jet Black
Fine Matte

Models and colors subject to change

North America

Minneapolis, MN

Mexico City, Mexico

Toronto, Canada

Tel: +1.763.421.2240

Tel: +52.55.5280.1449

Tel: +1.416.289.2770

hoffman@nvent.com



[HOFFMAN.nVent.com](https://hoffman.nVent.com)