



Single phase switched PDU	
Input Rating	: 20A, 110V
Outlet	: 20A Rated US NEMA 5-20R x 24
Inlet	: 20A NEMA L5-20P plug
Cordset	: 3 meter UL 12AWG cordset
Protection	: 20A single pole hydraulic MCB x 1
Circuit Details	: Output 16A max. U.S # 1 - 24

Meter Features (WS Switched PDU)	
Local Display	: Field replaceable 2.8" color LCD with touchscreen
Bank Measurement	: Voltage (V), Current (A), energy (kWh) & power factor
Outlet Control	: Outlet Switch ON / OFF
Accuracy	: ±1% Billing-grade
IP Access	: via IP dongle, one IP Access up to 16 PDU Levels
Cascade	: Up to 16 PDU under single IP address via IP dongle
SNMP	: V2 / V3 via IP dongle
Sensor Port x 2	: Temp. Sensor / Temp. + Humid. Sensor
Chassis Material	: Steel
Chassis Color	: Black
Product Dimension	: 2.1 (W) x 3.1 (D) x 53.15 (H) mm
Net Weight	: 23.5 lbs
Packing dimension (for 2 PDUs)	: 4.3 (W) x 10.6 (D) x 70.6 (H) inch
PDU gross weight (for 2 PDUs)	: 55.4 lbs

EMC	Compliance	: FCC Part 15 Subpart B certified
Safety	Compliance	: cTUVus Mark to UL 60950-1:2007/R:2014-10 CAN/CSA-C22.2 No. 60950-1:2007/A2:2014-10 UL 62368-1:2014 CAN/CSA-C22.2 No. 62368-1:2014 UL 60730-1 Ed.5 (2016)
Environment	Compliance	: RoHS2 & REACH
Operating Temperature		: -5 to 60 °C
Storage Temperature		: -25 to 65 °C
Operating Altitude		: 0 to 2,000 m
Storage Altitude		: 0 to 15,000 m
Humidity		: 8 to 95% RH, non-condensing