

Industrial Networking IDF

DUAL-ACCESS, FREE-STAND NETWORKING CABINET

VERSATILE AND ECONOMIC INDUSTRIAL NETWORKING CABINET. FULLY ACCESSORIZED, TESTED, CERTIFIED, AND READY TO BE DELIVERED

Dual-Access, Free-Standing Industrial Networking cabinet is designed to house and protect networking equipment and cables that are placed in challenging environments. It comes in a wide range of standard heights, widths and depths. It is fully tested and certified for National and International applications. The cabinet provides easy access to 19-in. rack mounted equipment and cables. The cabinet is offered in UL 508A Type 12 and 4X configurations.

The cabinet is offered in painted steel for UL 508A Type 12 applications and stainless steel (Type 304) for UL 508A Type 4X applications. Rack angles are fully RU marked on all sides and provided with square holes (.375-in. x .375-in.) per EIA standards. The rack angles are fully adjustable front to rear in a unitized, easy-to-move fashion.

Dual-Access, Free-Standing Type 12 and 4X cabinets are ideal for securing and protecting rack equipment that is used in applications with wet, hot, and dusty environments. Now provided in options with a cutout for an air conditioner offering up to 12,000 BTU cooling capacity – AC unit must be ordered separately.



KEY FEATURES

- UL 508A Type 12 or 4X offering
- 12 gauge mild or 304 stainless steel construction
- Tool-free hinge pins on doors for easy removal
- Locking door handles
- 19-in. rack angles spaced per EIA standards with RU marked square holes (.375-in. x .375-in.)
- Phosphatized steel coated with polyester paint (Black or Gray)
- Fully accessorized
- Dual access for easy access to equipment
- Broad, ready-to-order, AC-ready configuration
 - Precut hole for AC on side of cabinet
 - Order AC separately

APPLICATIONS INCLUDE:

- Plant floor automation
- Industrial Networking
- Petrochemical and Processing
- Corrosive environments
- Food and Beverage

SPECIFICATIONS

UNI-BODY CONSTRUCTION

- Heavy gauge multi-formed steel
- Seams continuously welded and ground smooth

FRONT / REAR DOOR

- Solid door with vault style 3-point latching system and keylocking handle
- Left-hinged doors

AC READY MODELS

- Provided with a cutout for an AC (G52) on the right side – order AC unit separately

RACK ANGLES

- 2 sets of EIA universal spaced with square holes (.375-in. x .375-in.).
- Fully adjustable front to rear and RU marked on all sides

INTERNAL ACCESSORIES

- Print Pocket on front door
- Vertical Cable Managers on 32-in. wide offering
- Cable tie-downs in strategic locations

SEISMIC RATED

- Tested per NEBS-Telecordia GR-63-CORE Zone 4, OSHPD pre-approved, meets CBC requirements



Stainless Steel



Mild Steel



Order AC unit separately

North America

Minneapolis, MN
Tel: +1.763.421.2240
Mexico City, Mexico
Tel: +52.55.5280.1449
Toronto, Canada
Tel: +1.416.289.2770

South America

Sao Paulo, Brazil
Tel: +55.11.5184.2100
Boituva, Brazil
Tel: +55.15.3363.9148

Europe

Betschdorf, France
Tel: +33.3.88.90.64.90
Straubenhardt, Germany
Tel: +49.7082.794.0
Dzierzoniow, Poland
Tel: +48.74.64.63.900
Lainate, Italy
Tel: +39.02.932.7141

Middle East & Africa

Dubai, United Arab Emirates
Tel: +971.4.378.1700
Bangalore, India
Tel: +91.80.6715.2001

Asia

Shanghai, P.R. China
Tel: +86.21.2412.6943
Singapore
Tel: +65.6768.5800
Shin-Yokohama, Japan
Tel: +81.45.476.0271
Seoul, Korea
Tel: +82.2.2129.7755
Qingdao
Tel: +86.532.8771.6101



Our powerful portfolio of brands:

nVent.com

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER