

TYPE 12 FREE-STANDING ENCLOSURES ACCESSORY SELECTION

FREE-STAND TYPE 12 ONE-DOOR

(See Accessories for Details)

				One-Door Single-Access Enclosures										One-Door Dual Access Enclosures											
				A602418FS	A722418FS	A723018FS	A723618FS	A902420FS	A903620FS	A603624FS	A722424FS	A723024FS	A723624FS	A903624FS	A723630FS	A723636FS	A903636FS	A722424FSDA	A723024FSDA	A723624FSDA	A903624FSDA	A722430FSDA	A722436FSDA	A723636FSDA	A903636FSDA
Steel	Conductive	Description	Panel Size																						
A60P24F1	A60P24F1G	Full Panel	48.00 x 20.00 (1219 x 508)	*	*a			*a									*a					*a	*a		
A60P24F2	A60P24F2G	Half Panel	24.88 x 20.00 (632 x 508)	*				*a									*a					*a	*a		
A72P24F1	A72P24F1G	Full Panel	60.00 x 20.00 (1524 x 508)		*			*a			*											*	*		
A72P24F2	A72P24F2G	Half Panel	30.88 x 20.00 (784 x 508)	*a	*			*a			*											*	*		
A90P24F1	A90P24F1G	Full Panel	78.00 x 20.00 (1981 x 508)					*														*	*		
A90P24F2	A90P24F2G	Half Panel	39.00 x 20.00 (1013 x 508)	*a	*a			*			*a							*a				*a	*a		
A72P30F1	A72P30F1G	Full Panel	60.00 x 26.00 (1524 x 660)			*					*							*							
A72P30F2	A72P30F2G	Half Panel	30.88 x 26.00 (784 x 660)			*					*							*							
A60P36F1	A60P36F1G	Full Panel	48.00 x 32.00 (1219 x 813)				*a		*a	*			*a	*a	*a	*a				*a	*a			*a	
A60P36F2	A60P36F2G	Half Panel	24.88 x 32.00 (632 x 813)				*a		*a	*			*a	*a	*a	*a				*a	*a			*a	
A72P36F1	A72P36F1G	Full Panel	60.00 x 32.00 (1524 x 813)			*					*		*a	*	*	*a				*	*a			*	*
A72P36F2	A72P36F2G	Half Panel	30.88 x 32.00 (784 x 813)			*		*a	*a	*a			*	*a	*	*a				*	*a			*	*
A90P36F1	A90P36F1G	Full Panel	78.00 x 32.00 (1981 x 813)					*					*	*	*	*				*	*			*	*
A90P36F2	A90P36F2G	Half Panel	39.88 x 32.00 (1013 x 813)				*a		*	*a			*a	*	*a	*a				*a	*a			*a	*

PANELS

Catalog Number

Steel	Conductive	Description	Panel Size
A60P24F1	A60P24F1G	Full Panel	48.00 x 20.00 (1219 x 508)
A60P24F2	A60P24F2G	Half Panel	24.88 x 20.00 (632 x 508)
A72P24F1	A72P24F1G	Full Panel	60.00 x 20.00 (1524 x 508)
A72P24F2	A72P24F2G	Half Panel	30.88 x 20.00 (784 x 508)
A90P24F1	A90P24F1G	Full Panel	78.00 x 20.00 (1981 x 508)
A90P24F2	A90P24F2G	Half Panel	39.00 x 20.00 (1013 x 508)
A72P30F1	A72P30F1G	Full Panel	60.00 x 26.00 (1524 x 660)
A72P30F2	A72P30F2G	Half Panel	30.88 x 26.00 (784 x 660)
A60P36F1	A60P36F1G	Full Panel	48.00 x 32.00 (1219 x 813)
A60P36F2	A60P36F2G	Half Panel	24.88 x 32.00 (632 x 813)
A72P36F1	A72P36F1G	Full Panel	60.00 x 32.00 (1524 x 813)
A72P36F2	A72P36F2G	Half Panel	30.88 x 32.00 (784 x 813)
A90P36F1	A90P36F1G	Full Panel	78.00 x 32.00 (1981 x 813)
A90P36F2	A90P36F2G	Half Panel	39.88 x 32.00 (1013 x 813)

SWING-OUT PANELS

Catalog No.	Description	Panel Size
A72SP24F3	Full Panel	60.00 x 18.81 (1524 x 478)
A72SP24F4	Half Panel ^b	30.88 x 18.81 (784 x 478)
A72AP30F3	Full Panel	60.00 x 24.81 (1524 x 630)
A72AP30F4	Half Panel ^b	30.88 x 24.81 (784 x 630)
A72SP36F3	Full Panel	60.00 x 30.81 (1524 x 783)
A72SP36F4	Half Panel ^b	30.88 x 30.81 (784 x 783)
A90SP36F3	Full Panel	78.00 x 30.81 (1981 x 783)
A90SP36F4	Half Panel ^b	39.88 x 30.81 (1013 x 783)

A602418FS	A722418FS	A723018FS	A723618FS	A902420FS	A903620FS	A603624FS	A722424FS	A723024FS	A723624FS	A903624FS	A723630FS	A723636FS	A903636FS	A722424FSDA	A723024FSDA	A723624FSDA	A903624FSDA	A722430FSDA	A722436FSDA	A723636FSDA	A903636FSDA			
	*							*						*					*	*				
	*							*						*					*	*				
		*						*			*	*	*		*			*	*		*	*		*
		*						*		*	*	*	*		*		*	*		*	*		*	*
		*						*		*	*	*	*		*		*	*		*	*		*	*
		*						*		*	*	*	*		*		*	*		*	*		*	*
		*						*		*	*	*	*		*		*	*		*	*		*	*
		*						*		*	*	*	*		*		*	*		*	*		*	*

SIDE-MOUNT PANELS

Steel	Conductive	Description	Panel Size
A60SMP14	A60SMP14G	14 Wide Panel (356)	48.00 x 14.00 (1219 x 356)
A72SMP14	A72SMP14G	14 Wide Panel (356)	60.00 x 14.00 (1524 x 356)
A90SMP14	A90SMP14G	14 Wide Panel (356)	78.00 x 14.00 (1981 x 356)
A72SMP20	A72SMP20G	20 Wide Panel (508)	60.00 x 20.00 (1524 x 508)
A90SMP20	A90SMP20G	20 Wide Panel (508)	78.00 x 20.00 (1981 x 508)

A602418FS	A722418FS	A723018FS	A723618FS	A902420FS	A903620FS	A603624FS	A722424FS	A723024FS	A723624FS	A903624FS	A723630FS	A723636FS	A903636FS	A722424FSDA	A723024FSDA	A723624FSDA	A903624FSDA	A722430FSDA	A722436FSDA	A723636FSDA	A903636FSDA			
*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*
*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*
*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*
*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*
*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*
*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*

HEAVY-DUTY PANEL SUPPORTS

Catalog No.	Description	Panel Size
A60FSHDPS	2 Full-Length Panel Supports	57.25 (1454)
A72FSHDPS	2 Full-Length Panel Supports	69.25 (1759)
A90FSHDPS	2 Full-Length Panel Supports	87.25 (2216)

A602418FS	A722418FS	A723018FS	A723618FS	A902420FS	A903620FS	A603624FS	A722424FS	A723024FS	A723624FS	A903624FS	A723630FS	A723636FS	A903636FS	A722424FSDA	A723024FSDA	A723624FSDA	A903624FSDA	A722430FSDA	A722436FSDA	A723636FSDA	A903636FSDA			
*	*	*	*	*	*	*a	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*
*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*
*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*
*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*
*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*
*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*

Millimeter dimensions are in parentheses ()
^a Requires heavy-duty panel supports
^b Fits in top half or bottom half of enclosure

FREE-STANDING TYPE 12 TWO-DOOR

(See Accessories for Details)

PANELS

Catalog Number

Steel	Conductive	Description	Panel Size	Two-Door Single-Access Enclosures								Two-Door Dual Access Enclosures							
				A604818FSD	A724818FSD	A726018FSD	A727218FSD	A904820FSD	A907220FSD	A724824FSD	A726024FSD	A727224FSD	A907224FSD	A726036FSD	A907236FSD	A724824FSDAD	A726024FSDAD	A727224FSDAD	A907224FSDAD
A60P24F1	A60P24F1G	Full Panel	48.00 x 20.00 (1219 x 508)	.b	.a.b			.a.b	.a.b					.a.b					
A60P24F2	A60P24F2G	Half Panel	24.88 x 20.00 (632 x 508)	.b	.a.b			.a.b	.a.b					.a.b					
A72P24F1	A72P24F1G	Full Panel	60.00 x 20.00 (1524 x 508)		.b			.a.b	.b					.b					
A72P24F2	A72P24F2G	Half Panel	30.88 x 20.00 (784 x 508)	.a.b	.b			.a.b	.b					.b					
A90P24F1	A90P24F1G	Full Panel	78.00 x 20.00 (1981 x 508)					.b											
A90P24F2	A90P24F2G	Half Panel	39.00 x 20.00 (1013 x 508)	.a.b	.a.b			.b	.a.b					.a.b					
A72P30F1	A72P30F1G	Full Panel	60.00 x 26.00 (1524 x 660)			.b			.b					.b				.b	
A72P30F2	A72P30F2G	Half Panel	30.88 x 26.00 (784 x 660)			.b			.b					.b				.b	
A60P36F1	A60P36F1G	Full Panel	48.00 x 32.00 (1219 x 813)				.a.b	.a.b		.a.b	.a.b	.a.b	.a.b			.a.b	.a.b	.a.b	.a.b
A60P36F2	A60P36F2G	Half Panel	24.88 x 32.00 (632 x 813)				.a.b	.a.b		.a.b	.a.b	.a.b	.a.b			.a.b	.a.b	.a.b	.a.b
A72P36F1	A72P36F1G	Full Panel	60.00 x 32.00 (1524 x 813)				.b	.a.b		.b	.a.b	.a.b	.a.b			.b	.a.b	.a.b	.a.b
A72P36F2	A72P36F2G	Half Panel	30.88 x 32.00 (784 x 813)				.b	.a.b		.b	.a.b	.a.b	.a.b			.b	.a.b	.a.b	.a.b
A90P36F1	A90P36F1G	Full Panel	78.00 x 32.00 (1981 x 813)				.b	.a.b		.b	.a.b	.a.b	.a.b			.b	.a.b	.a.b	.a.b
A90P36F2	A90P36F2G	Half Panel	39.88 x 32.00 (1013 x 813)				.a.b	.a.b		.a.b	.a.b	.a.b	.a.b			.a.b	.a.b	.a.b	.a.b

SWING-OUT PANELS

Catalog No.	Description	Panel Size	A604818FSD	A724818FSD	A726018FSD	A727218FSD	A904820FSD	A907220FSD	A724824FSD	A726024FSD	A727224FSD	A907224FSD	A726036FSD	A907236FSD	A724824FSDAD	A726024FSDAD	A727224FSDAD	A907224FSDAD	A726036FSDAD
A72SP24F3	Full Panel	60.00 x 18.81 (1524 x 478)		.b					.b						.b				
A72SP24F4	Half Panel ^b	30.88 x 18.81 (784 x 478)		.b					.b						.b				
A72AP30F3	Full Panel	60.00 x 24.81 (1524 x 630)			.b				.b				.b		.b				.b
A72AP30F4	Half Panel ^b	30.88 x 24.81 (784 x 630)			.b				.b				.b		.b				.b
A72SP36F3	Full Panel	60.00 x 30.81 (1524 x 783)			.b				.b	.a.b							.b		.b
A72SP36F4	Half Panel ^b	30.88 x 30.81 (784 x 783)			.b				.b	.a.b							.b		.b
A90SP36F3	Full Panel	78.00 x 30.81 (1981 x 783)					.b			.b			.b					.b	
A90SP36F4	Half Panel ^b	39.88 x 30.81 (1013 x 783)					.b			.b			.b					.b	

SIDE-MOUNT PANELS

Steel	Conductive	Description	Panel Size	A604818FSD	A724818FSD	A726018FSD	A727218FSD	A904820FSD	A907220FSD	A724824FSD	A726024FSD	A727224FSD	A907224FSD	A726036FSD	A907236FSD	A724824FSDAD	A726024FSDAD	A727224FSDAD	A907224FSDAD	A726036FSDAD
A60SMP14	A60SMP14G	14 Wide Panel (356)	48.00 x 14.00 (1219 x 356)	.d					
A72SMP14	A72SMP14G	14 Wide Panel (356)	60.00 x 14.00 (1524 x 356)		.d	.d	.d	.d												.
A90SMP14	A90SMP14G	14 Wide Panel (356)	78.00 x 14.00 (1981 x 356)				
A72SMP20	A72SMP20G	20 Wide Panel (508)	60.00 x 20.00 (1524 x 508)					.d	.d	.d	.d	.d
A90SMP20	A90SMP20G	20 Wide Panel (508)	78.00 x 20.00 (1981 x 508)							.d	.d	.d

HEAVY-DUTY PANEL SUPPORTS

Catalog No.	Description	Panel Size	A604818FSD	A724818FSD	A726018FSD	A727218FSD	A904820FSD	A907220FSD	A724824FSD	A726024FSD	A727224FSD	A907224FSD	A726036FSD	A907236FSD	A724824FSDAD	A726024FSDAD	A727224FSDAD	A907224FSDAD	A726036FSDAD	
A60FSHDPS	2 Full-Length Panel Supports	57.25 (1454)	.b																	
A72FSHDPS	2 Full-Length Panel Supports	69.25 (1759)		.b	.b	.b	.b		.b	.b	.b	.b	.b	.b		.b	.b	.b	.b	.b
A90FSHDPS	2 Full-Length Panel Supports	87.25 (2216)					.b	.b				.b	.b	.b					.b	.b

Millimeter dimensions are in parentheses ()

^a Requires heavy-duty panel supports

^b Requires center panel supports

^c Fits in top half or bottom half of enclosure

^d Will not fit if other panels are also installed in the same enclosure

FREE-STAND TYPE 12 ONE-DOOR

(See Accessories for Details)

				One-Door Single-Access Enclosures										One-Door Dual Access Enclosures											
				A602418FS	A722418FS	A723018FS	A723618FS	A902420FS	A903620FS	A603624FS	A722424FS	A723024FS	A723624FS	A903624FS	A723630FS	A723636FS	A903636FS	A722424FSDA	A723024FSDA	A723624FSDA	A903624FSDA	A722430FSDA	A722436FSDA	A723636FSDA	A903636FSDA
Steel	Conductive	Description	Panel Size																						
A60P48F1	A60P48F1G	Full Panel	48.00 x 44.00 (1219 x 1118)																						
A72P48F1	A72P48F1G	Full Panel	60.00 x 44.00 (1524 x 1118)																						
A72P48F2	A72P48F2G	Half Panel	30.88 x 44.00 (784 x 1118)																						
A90P48F1	A90P48F1G	Full Panel	78.00 x 44.00 (1981 x 1118)																						
A90P48F2	A90P48F2G	Half Panel	39.88 x 44.00 (1013 x 1118)																						
A72P60F1	A72P60F1G	Full Panel	60.00 x 56.00 (1524 x 1422)																						
A72P60F2	A72P60F2G	Half Panel	30.88 x 56.00 (784 x 1422)																						
A72P72F1	A72P72F1G	Full Panel	60.00 x 68.00 (1524 x 1727)																						
A72P72F2	A72P72F2G	Half Panel	30.88 x 68.00 (784 x 1727)																						
A90P72F1	A90P72F1G	Full Panel	78.00 x 68.00 (1981 x 1727)																						
A90P72F2	A90P72F2G	Half Panel	39.88 x 68.00 (1013 x 1727)																						

PANELS

Catalog Number

Steel	Conductive	Description	Panel Size
A60P48F1	A60P48F1G	Full Panel	48.00 x 44.00 (1219 x 1118)
A72P48F1	A72P48F1G	Full Panel	60.00 x 44.00 (1524 x 1118)
A72P48F2	A72P48F2G	Half Panel	30.88 x 44.00 (784 x 1118)
A90P48F1	A90P48F1G	Full Panel	78.00 x 44.00 (1981 x 1118)
A90P48F2	A90P48F2G	Half Panel	39.88 x 44.00 (1013 x 1118)
A72P60F1	A72P60F1G	Full Panel	60.00 x 56.00 (1524 x 1422)
A72P60F2	A72P60F2G	Half Panel	30.88 x 56.00 (784 x 1422)
A72P72F1	A72P72F1G	Full Panel	60.00 x 68.00 (1524 x 1727)
A72P72F2	A72P72F2G	Half Panel	30.88 x 68.00 (784 x 1727)
A90P72F1	A90P72F1G	Full Panel	78.00 x 68.00 (1981 x 1727)
A90P72F2	A90P72F2G	Half Panel	39.88 x 68.00 (1013 x 1727)

CENTER PANEL SUPPORTS

Catalog No.	Description																								
A60FSCPS	Center Panel Support																								
A72FSCPS	Center Panel Support																								
A90FSCPS	Center Panel Support																								

CLAMPING NUTS

Catalog No.	Description																								
APS1420CN	1/4-20 Clamping Nut (Qty. 20) for special use	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*
APS51616CN	1/4-18 Clamping Nut (Qty. 20) for special use	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*

CASTERS

Catalog No.	Description	Size																							
DMCKC	Set of 4 Casters	4 high x 3 diameter	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*

19-IN. RACK PANELS

Catalog No.	Description	Rack Panel Size	Rack Units																						
P19RP1UA	Aluminum Rack Panel	19.00x1.75 (483x44)	1	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*
P19RP2UA	Aluminum Rack Panel	19.00x3.50 (483x89)	2	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*
P19RP3UA	Aluminum Rack Panel	19.00x5.25 (483 x133)	3	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*
P19RP4UA	Aluminum Rack Panel	19.00x7.00 (483x178)	4	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*
P19RP5UA	Aluminum Rack Panel	19.00x8.75 (483x222)	5	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*
P19RP6UA	Aluminum Rack Panel	19.00x10.50 (483x267)	6	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*
P19RP7UA	Aluminum Rack Panel	19.00x12.25 (483x311)	7	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*
P19RP8UA	Aluminum Rack Panel	19.00x14.00 (483x356)	8	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*
P19RP9UA	Aluminum Rack Panel	19.00x15.75 (483x400)	9	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*
P19RP10UA	Aluminum Rack Panel	19.00x17.50 (483x445)	10	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*
P19RP11UA	Aluminum Rack Panel	19.00x19.25 (483x489)	11	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*
P19RP12UA	Aluminum Rack Panel	19.00x21.00 (483x533)	12	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*
P24RP2UA	Aluminum Rack Panel	24.00x3.50 (610x89)	2	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*
P24RP3UA	Aluminum Rack Panel	24.00x5.25 (610x133)	3	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*
P24RP4UA	Aluminum Rack Panel	24.00x7.00 (610x178)	4	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*
P24RP8UA	Aluminum Rack Panel	24.00x14.00 (610x356)	8	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*

Millimeter dimensions are in parentheses ()

One rack unit= 1.75 in. (45mm)

^b Requires swing-out rack mounting frame

FREE-STAND TYPE 12 ONE-DOOR

(See Accessories for Details)

					One-Door Single-Access Enclosures										One-Door Dual Access Enclosures											
					A602418FS	A722418FS	A723018FS	A723618FS	A902420FS	A903620FS	A603624FS	A722424FS	A723024FS	A723624FS	A903624FS	A723630FS	A723636FS	A903636FS	A722424FSDA	A723024FSDA	A723624FSDA	A903624FSDA	A722430FSDA	A722436FSDA	A723636FSDA	A903636FSDA
Catalog No.	Description	For Rack Size	No. Units ^a	Angle Length																						
A60RP24F5	2 Full-Length Angles	19 (483)	28	49.00 (1245)	*	*			*				*					*				*	*			
A60RP24F6	2 Half-Length Angles	19 (483)	15	26.25 (677)	*	*			*				*					*				*	*			
A72RP24F5	2 Full-Length Angles	19 (483)	35	61.25 (1556)	*	*			*				*					*				*	*			
A72RP24F6	2 Half-Length Angles	19 (483)	18	31.50 (800)	*	*			*				*					*				*	*			
A90RP24F5	2 Full-Length Angles	19 (483)	45	78.75 (2000)					*				*					*				*	*			
A90RP24F6	2 Half-Length Angles	19 (483)	23	40.25 (1022)	*	*			*				*					*				*	*			
A72RP30F5	2 Full-Length Angles	24 (610)	35	61.25 (1556)			*						*					*				*	*			
A72RP30F6	2 Half-Length Angles	24 (610)	18	31.50 (800)			*						*					*				*	*			

RACK-MOUNT ANGLES L-STYLE (TYPE RP) FOR 19- AND 24-IN. EQUIPMENT
RACK MOUNTING ANGLES U-STYLE (TYPE RA) FOR 19- AND 24-IN. EQUIPMENT

Catalog No.	Description	For Rack Size	No. Units ^a	Angle Length																					
A60RA19TH	2 Full-Length Angles	19 (483)	28	49.00 (1245)	*	*			*				*					*				*	*		
A72RA19TH	2 Full-Length Angles	19 (483)	35	61.25 (1556)		*			*				*					*				*	*		
A90RA19TH	2 Full-Length Angles	19 (483)	45	78.75 (2000)					*				*					*				*	*		
A72RA24TH	2 Full-Length Angles	24 (610)	35	61.25 (1556)			*						*					*				*	*		

CLIP NUT PACKAGE

Catalog No.	Description	Size	Fits																					
AN1032	Clip Nut (Pkg. 20)	#10-32 Zinc Plated	RA Type Mnt. Angles	*	*	*		*		*	*	*	*	*	*	*	*	*	*	*	*	*	*	*

19-IN. SWING-OUT RACK MOUNTING FRAMES

Catalog No.	Description	For Rack Size	No. Units ^a	Angle Length																					
A7230S0F19	Full Swing-Out Frame	19 (483)	33	57.88 (1470)		*	*		*				*					*				*	*		
A7236S0F19	Full Swing-Out Frame	19 (483)	33	57.88 (1470)		*	*	*		*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*
A9036S0F19	Full Swing-Out Frame	19 (483)	43	75.36 (1915)			*		*				*					*				*	*		*

RACK-ANGLE MOUNTED DRAWERS*

Catalog No.	Description	For Rack Size	Rack Units																					
P19DR1US	Drawer	19.00 (483)	1	*	*	*		*		*		*		*		*	*	*	*	*	*	*	*	*
P19DR2US	Drawer	19.00 (483)	2	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*
P19DR3US	Drawer	19.00 (483)	3	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*

WRITING SURFACE*

Catalog No.	Description	Fits Drawer																					
P19WS	Hinged Surface	P12DR1US, P12DR2US, P19DR3US	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*

RACK-MOUNT SHELVES*

Catalog No.	Description	Shelf Size	For Rack Size	Rack Units																				
P19SHP68	Sliding Shelf	16.72X16.20 (425x412)	19.00 (483)	2	*	*	*		*		*		*		*		*	*	*	*	*	*	*	
P19SHP810	Sliding Shelf	24.59x16.20 (625x412)	19.00 (483)	2	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	

GUIDES FOR RACK-MOUNT EQUIPMENT*

Catalog No.	Description	Rack Units																					
AG1U6	Chassis Guides (2)	1	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*	*

Millimeter dimensions are in parentheses ()

One rack unit= 1.75 in. (45mm)

^a Will not fit if other panels are also installed in same enclosure

* Requires Rack Angles

FREE-STANDING TYPE 12 TWO-DOOR

(See Accessories for Details)

					Two-Door Single-Access Enclosures						Two-Door Dual Access Enclosures										
					A604818FSD	A724818FSD	A726018FSD	A727218FSD	A904820FSD	A907220FSD	A724824FSD	A726024FSD	A727224FSD	A907224FSD	A726036FSD	A907236FSD	A724824FSDAD	A726024FSDAD	A727224FSDAD	A907224FSDAD	A726036FSDAD
A60RP24F5	2 Full-Length Angles	19 (483)	28	49.00 (1245)	*b	*b			*b	*b						*b					
A60RP24F6	2 Half-Length Angles	19 (483)	15	26.25 (677)	*b																
A72RP24F5	2 Full-Length Angles	19 (483)	35	61.25 (1556)		*b				*b						*b					
A72RP24F6	2 Half-Length Angles	19 (483)	18	31.50 (800)	*b	*b				*b						*b					
A90RP24F5	2 Full-Length Angles	19 (483)	45	78.75 (2000)						*b											
A90RP24F6	2 Half-Length Angles	19 (483)	23	40.25 (1022)	*b	*b				*b						*b					
A72RP30F5	2 Full-Length Angles	24 (610)	35	61.25 (1556)			*b				*b			*b			*b				*b
A72RP30F6	2 Half-Length Angles	24 (610)	18	31.50 (800)			*b				*b						*b				*b

RACK-MOUNT ANGLES L-STYLE (TYPE RP) FOR 19- AND 24-IN. EQUIPMENT

Catalog No.	Description	For Rack Size	No. Units ^a	Angle Length
A60RP24F5	2 Full-Length Angles	19 (483)	28	49.00 (1245)
A60RP24F6	2 Half-Length Angles	19 (483)	15	26.25 (677)
A72RP24F5	2 Full-Length Angles	19 (483)	35	61.25 (1556)
A72RP24F6	2 Half-Length Angles	19 (483)	18	31.50 (800)
A90RP24F5	2 Full-Length Angles	19 (483)	45	78.75 (2000)
A90RP24F6	2 Half-Length Angles	19 (483)	23	40.25 (1022)
A72RP30F5	2 Full-Length Angles	24 (610)	35	61.25 (1556)
A72RP30F6	2 Half-Length Angles	24 (610)	18	31.50 (800)

RACK MOUNTING ANGLES U-STYLE (TYPE RA) FOR 19- AND 24-IN. EQUIPMENT

Catalog No.	Description	For Rack Size	No. Units ^a	Angle Length
A60RA19TH	2 Full-Length Angles	19 (483)	28	49.00 (1245)
A72RA19TH	2 Full-Length Angles	19 (483)	35	61.25 (1556)
A90RA19TH	2 Full-Length Angles	19 (483)	45	78.75 (2000)
A72RA24TH	2 Full-Length Angles	24 (610)	35	61.25 (1556)

CLIP NUT PACKAGE

Catalog No.	Description	Size	Fits
AN1032	Clip Nut (Pkg. 20)	#10-32 Zinc Plated	RA Type Mnt. Angles

19-IN. SWING-OUT RACK MOUNTING FRAMES

Catalog No.	Description	For Rack Size	No. Units ^a	Angle Length
A7230S0F19	Full Swing-Out Frame	19 (483)	33	57.88 (1470)
A7236S0F19	Full Swing-Out Frame	19 (483)	33	57.88 (1470)
A9036S0F19	Full Swing-Out Frame	19 (483)	43	75.36 (1915)

RACK-ANGLE MOUNTED DRAWERS*

Catalog No.	Description	For Rack Size	Rack Units
P19DR1US	Drawer	19.00 (483)	1
P19DR2US	Drawer	19.00 (483)	2
P19DR3US	Drawer	19.00 (483)	3

WRITING SURFACE*

Catalog No.	Description	Fits Drawer
P19WS	Hinged Surface	P12DR1US, P12DR2US, P19DR3US

RACK-MOUNT SHELVES*

Catalog No.	Description	Shelf Size	For Rack Size	Rack Units
P19SHP68	Sliding Shelf	16.72X16.20 (425x412)	19.00 (483)	2
P19SHP810	Sliding Shelf	24.59x16.20 (625x412)	19.00 (483)	2

GUIDES FOR RACK-MOUNT EQUIPMENT*

Catalog No.	Description	Rack Units
AG1U6	Chassis Guides (2)	1

Millimeter dimensions are in parentheses ()
 One rack unit= 1.75 in. (45mm)
^a Will not fit if other panels are also installed in same enclosure
^b Requires heavy-duty panel supports
 * Requires Rack Angles

SEISMIC ACCESSORIES

(See Accessories for Details)

SEISMIC MOUNTING PLATE KITS

Catalog No.	Description	Anchor Size	Two-Door, Single Access Enclosures										Two-Door, Dual Access Enclosures						
			A604818SSFSD	A724818SSFSD	A726018SSFSD	A727218SSFSD	A904820SSFSD	A907220SSFSD	A724824SSFSD	A726024SSFSD	A727224SSFSD	A907224SSFSD	A726036SSFSD	A907236SSFSD	A724824FSDAD	A726024FSDAD	A727224FSDAD	A907224FSDAD	A726036FSDAD
ASMP12SS	Seismic Mounting Plate, SS, 1/2 in.	1/2 in.																	
ASMP58SS	Seismic Mounting Plate, SS, 5/8 in.	5/8 in.																	
ASMP34SS	Seismic Mounting Plate, SS, 3/4 in.	3/4 in.																	

SEISMIC PANEL MOUNTING KITS

Catalog No.	Description	Fits Enclosure A in. (mm)																	
ASPANKIT60	Seismic Panel Mounting Kit, 60 in.	60.00 (1524)																	
ASPANKIT72	Seismic Panel Mounting Kit, 72 in.	72.00 (1829)																	
ASPANKIT90	Seismic Panel Mounting Kit, 90 in.	90.00 (2286)																	

PANELS, FULL

Catalog Number		Panel Size in. (mm)	Fits Enclosure A x B in. (mm)																	
Steel	Conductive																			
A60P24F1	A60P24F1G	48.00 x 20.00 (1219 x 508)	60.00 x 24.00 (1524 x 610)																	
A72P24F1	A72P24F1G	60.00 x 20.00 (1524 x 508)	72.00 x 24.00 (1829 x 610)																	
A90P24F1	A90P24F1G	78.00 x 20.00 (1981 x 508)	90.00 x 24.00 (2286 x 610)																	
A72P30F1	A72P30F1G	60.00 x 26.00 (1524 x 660)	72.00 x 30.00 (1829 x 762)																	
A60P36F1	A60P36F1G	48.00 x 32.00 (1219 x 813)	60.00 x 36.00 (1524 x 914)																	
A72P36F1	A72P36F1G	60.00 x 32.00 (1524 x 813)	72.00 x 36.00 (1829 x 914)																	
A90P36F1	A90P36F1G	78.00 x 32.00 (1981 x 813)	90.00 x 36.00 (2286 x 914)																	

RACK MOUNTING ANGLES, L-STYLE (TYPE RP), FULL LENGTH

Catalog No.	Fits Enclosure A x B in. (mm)	For Rack Size in. (mm)																	
A60RP24F5	60.00 x 24.00 (1524 x 610)	19.00 (483)																	
A72RP24F5	72.00 x 24.00 (1829 x 610)	19.00 (483)																	
A72RP30F5	72.00 x 30.00 (1829 x 762)	24.00 (610)																	
A90RP24F5	90.00 x 24.00 (2286 x 610)	19.00 (483)																	