

## INDUSTRY-EXCLUSIVE ENCLOSURE OFFERING THAT COMPLIES WITH NSF-INTERNATIONAL REQUIREMENTS

### A PATENTED COMBINATION OF CRITICAL SANITARY FEATURES AND INNOVATIVE DESIGN

WaterShed enclosures provide superior protection for process controls in harsh washdown environments, while minimizing potential contamination catch-points. Featuring a unique patented design, WaterShed is the only enclosure offering that meets the stringent sanitary certification requirements of NSF International. The combination of the sloped top and the angled door flange significantly reduces areas where liquids can pool and bacteria can form.



### KEY FEATURES

- **Over 40 standard sizes in free-standing and wall-mount models**
- **Easy-to-clean design**
  - NSF certified
  - Lift-off bullet hinges
  - Sanitary leg kits
  - Sanitary stand-off kits
- **Eliminates bacteria harboring opportunities**
  - 20-degree sloped top
  - Sloped-door flange with trough collar shielded bullet hinge and seamless gasket
  - Beveled-door edges
- **Premium corrosion resistance**
  - Stainless steel latching and hardware
  - Stainless steel PowerGlide handle; UL 4X rated
  - Continuous foam-in-place gasket
  - Manufactured from 304 stainless steel

### APPLICATIONS INCLUDE:

- Food and Beverage
- Sanitary
- Washdown production

# WaterShed enclosures

## MODIFYING YOUR ENCLOSURE

### ACCESSORIES

To accommodate diverse application requirements, a variety of accessories are available:

- Mounting bracket kit
- Panels for Type 3R, 4, 4X, 12 and 13 enclosures
- Stand-off kit
- Padlocking handle kit
- Padlocking latch kit
- H2Omit vent drains, Type 4x
- H2Omit thermoelectric dehumidifier

### DESIGN YOUR STANDARD

nVent HOFFMAN excels at modifying and customizing products to your specifications.

For more information or to learn about our modifications services, contact your local HOFFMAN sales office or distributor.



Stand-off kit for wall-mount enclosures



Sanitary leg kit; contact area with floor is less than one square-inch per leg

### North America

Minneapolis, MN  
Tel: +1.763.421.2240

Mexico City, Mexico  
Tel: +52.55.5280.1449

Toronto, Canada  
Tel: +1.416.289.2770

### South America

Sao Paulo, Brazil  
Tel: +55.11.5184.2100

Boitura, Brazil  
Tel: +55.15.3363.9148

### Europe

Betschdorf, France  
Tel: +33.3.88.90.64.90

Straubenhardt, Germany  
Tel: +49.7082.794.0

Dzierzoniow, Poland  
Tel: +48.74.64.63.900

Assago, Italy  
Tel: +39.02.5776151.224

### Middle East & India

Dubai, United Arab Emirates  
Tel: +971.4.378.1700

Bangalore, India  
Tel: +91.80.6715.2001

### Asia

Shanghai, P.R. China  
Tel: +86.21.2412.6943

Singapur  
Tel: +65.6768.5800

Shin-Yokohama, Japan  
Tel: +81.45.476.0271

Seoul, Korea  
Tel: +82.2.2129.7755

Qingdao  
Tel: +86.532.8771.6101



Our powerful portfolio of brands:

[nVent.com](http://nVent.com)

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER