
















SELECTION MATRIX: RACK MOUNTING

										
Frame Catalog Number	H (mm)	W (mm)	D (mm)	Bay Count	19-inch Rack Angle (Square Hole)	19-inch Rack Angle (Tapped Hole)	Adjustable Rack-Mount Rails	Frame Reducing Bracket 19-inch Centered	Frame Reducing Bracket 19-inch Justified	Frame Accessory Bracket
P2F664	600	600	400	Single	P2RA19S6	P2RA19T6	P2GARA4	N/A	N/A	P2AFB19
P2F666	600	600	600	Single	P2RA19S6	P2RA19T6	P2GARA6	N/A	N/A	P2AFB19
P2F688	600	800	800	Single	P2RA19S6	P2RA19T6	P2GARA8	P2AFRB100	P2AFRB200	P2AFB19
P2F864	800	600	400	Single	P2RA19S8	P2RA19T8	P2GARA4	N/A	N/A	P2AFB19
P2F866	800	600	600	Single	P2RA19S8	P2RA19T8	P2GARA6	N/A	N/A	P2AFB19
P2F888	800	800	800	Single	P2RA19S8	P2RA19T8	P2GARA8	P2AFRB100	P2AFRB200	P2AFB19
P2F1064	1000	600	400	Single	P2RA19S10	P2RA19T10	P2GARA4	N/A	N/A	P2AFB19
P2F1065	1000	600	500	Single	P2RA19S10	P2RA19T10	P2GARA5	N/A	N/A	P2AFB19
P2F1066	1000	600	600	Single	P2RA19S10	P2RA19T10	P2GARA6	N/A	N/A	P2AFB19
P2F1085	1000	800	500	Single	P2RA19S10	P2RA19T10	P2GARA5	P2AFRB100	P2AFRB200	P2AFB19
P2F1086	1000	800	600	Single	P2RA19S10	P2RA19T10	P2GARA6	P2AFRB100	P2AFRB200	P2AFB19
P2F1088	1000	800	800	Single	P2RA19S10	P2RA19T10	P2GARA8	P2AFRB100	P2AFRB200	P2AFB19
P2F10125	1000	1200	500	Double	P2RA19S10	P2RA19T10	P2GARA5	N/A	N/A	P2AFB19
P2F1264	1200	600	400	Single	P2RA19S12	P2RA19T12	P2GARA4	N/A	N/A	P2AFB19
P2F1265	1200	600	500	Single	P2RA19S12	P2RA19T12	P2GARA5	N/A	N/A	P2AFB19
P2F1266	1200	600	600	Single	P2RA19S12	P2RA19T12	P2GARA6	N/A	N/A	P2AFB19
P2F1285	1200	800	500	Single	P2RA19S12	P2RA19T12	P2GARA5	P2AFRB100	P2AFRB200	P2AFB19
P2F1286	1200	800	600	Single	P2RA19S12	P2RA19T12	P2GARA6	P2AFRB100	P2AFRB200	P2AFB19
P2F1288	1200	800	800	Single	P2RA19S12	P2RA19T12	P2GARA8	P2AFRB100	P2AFRB200	P2AFB19
P2F12125	1200	1200	500	Double	P2RA19S12	P2RA19T12	P2GARA5	N/A	N/A	P2AFB19
P2F1465	1400	600	500	Single	P2RA19S14	P2RA19T14	P2GARA5	N/A	N/A	P2AFB19
P2F1466	1400	600	600	Single	P2RA19S14	P2RA19T14	P2GARA6	N/A	N/A	P2AFB19
P2F1468	1400	600	800	Single	P2RA19S14	P2RA19T14	P2GARA8	N/A	N/A	P2AFB19
P2F1485	1400	800	500	Single	P2RA19S14	P2RA19T14	P2GARA5	P2AFRB100	P2AFRB200	P2AFB19
P2F1486	1400	800	600	Single	P2RA19S14	P2RA19T14	P2GARA6	P2AFRB100	P2AFRB200	P2AFB19
P2F1488	1400	800	800	Single	P2RA19S14	P2RA19T14	P2GARA8	P2AFRB100	P2AFRB200	P2AFB19
P2F14125	1400	1200	500	Double	P2RA19S14	P2RA19T14	P2GARA5	N/A	N/A	P2AFB19
P2F1664	1600	600	400	Single	P2RA19S16	P2RA19T16	P2GARA4	N/A	N/A	P2AFB19
P2F1665	1600	600	500	Single	P2RA19S16	P2RA19T16	P2GARA5	N/A	N/A	P2AFB19
P2F1666	1600	600	600	Single	P2RA19S16	P2RA19T16	P2GARA6	N/A	N/A	P2AFB19
P2F1668	1600	600	800	Single	P2RA19S16	P2RA19T16	P2GARA8	N/A	N/A	P2AFB19
P2F1684	1600	800	400	Single	P2RA19S16	P2RA19T16	P2GARA4	P2AFRB100	P2AFRB200	P2AFB19
P2F1685	1600	800	500	Single	P2RA19S16	P2RA19T16	P2GARA5	P2AFRB100	P2AFRB200	P2AFB19
P2F1686	1600	800	600	Single	P2RA19S16	P2RA19T16	P2GARA6	P2AFRB100	P2AFRB200	P2AFB19
P2F1688	1600	800	800	Single	P2RA19S16	P2RA19T16	P2GARA8	P2AFRB100	P2AFRB200	P2AFB19
P2F16104	1600	1000	400	Single	P2RA19S16	P2RA19T16	P2GARA4	P2AFRB200	N/A	P2AFB19
P2F16106	1600	1000	600	Single	P2RA19S16	P2RA19T16	P2GARA6	P2AFRB200	N/A	P2AFB19
P2F16124	1600	1200	400	Double	P2RA19S16	P2RA19T16	P2GARA4	N/A	N/A	P2AFB19
P2F16125	1600	1200	500	Double	P2RA19S16	P2RA19T16	P2GARA5	N/A	N/A	P2AFB19
P2F16126	1600	1200	600	Double	P2RA19S16	P2RA19T16	P2GARA6	N/A	N/A	P2AFB19
P2F16128	1600	1200	800	Double	P2RA19S16	P2RA19T16	P2GARA8	N/A	N/A	P2AFB19

										
Frame Catalog Number	H (mm)	W (mm)	D (mm)	Bay Count	19-inch Rack Angle (Square Hole)	19-inch Rack Angle (Tapped Hole)	Adjustable Rack-Mount Rails	Frame Reducing Bracket 19-inch Centered	Frame Reducing Bracket 19-inch Justified	Frame Accessory Bracket
P2F16164	1600	1600	400	Double	P2RA19S16	P2RA19T16	P2GARA4	N/A	N/A	P2AFB19
P2F16165	1600	1600	500	Double	P2RA19S16	P2RA19T16	P2GARA5	N/A	N/A	P2AFB19
P2F16166	1600	1600	600	Double	P2RA19S16	P2RA19T16	P2GARA6	N/A	N/A	P2AFB19
P2F16168	1600	1600	800	Double	P2RA19S16	P2RA19T16	P2GARA8	N/A	N/A	P2AFB19
P2F1845	1800	400	500	Single	N/A	N/A	N/A	N/A	N/A	P2AFB19
P2F1846	1800	400	600	Single	N/A	N/A	N/A	N/A	N/A	P2AFB19
P2F1864	1800	600	400	Single	P2RA19S18	P2RA19T18	P2GARA4	N/A	N/A	P2AFB19
P2F1865	1800	600	500	Single	P2RA19S18	P2RA19T18	P2GARA5	N/A	N/A	P2AFB19
P2F1866	1800	600	600	Single	P2RA19S18	P2RA19T18	P2GARA6	N/A	N/A	P2AFB19
P2F1868	1800	600	800	Single	P2RA19S18	P2RA19T18	P2GARA8	N/A	N/A	P2AFB19
P2F1884	1800	800	400	Single	P2RA19S18	P2RA19T18	P2GARA4	P2AFRB100	P2AFRB200	P2AFB19
P2F1885	1800	800	500	Single	P2RA19S18	P2RA19T18	P2GARA5	P2AFRB100	P2AFRB200	P2AFB19
P2F1886	1800	800	600	Single	P2RA19S18	P2RA19T18	P2GARA6	P2AFRB100	P2AFRB200	P2AFB19
P2F1888	1800	800	800	Single	P2RA19S18	P2RA19T18	P2GARA8	P2AFRB100	P2AFRB200	P2AFB19
P2F18104	1800	1000	400	Single	P2RA19S18	P2RA19T18	P2GARA4	P2AFRB200	N/A	P2AFB19
P2F18105	1800	1000	500	Single	P2RA19S18	P2RA19T18	P2GARA5	P2AFRB200	N/A	P2AFB19
P2F18106	1800	1000	600	Single	P2RA19S18	P2RA19T18	P2GARA6	P2AFRB200	N/A	P2AFB19
P2F18108	1800	1000	800	Single	P2RA19S18	P2RA19T18	P2GARA8	P2AFRB200	N/A	P2AFB19
P2F18124	1800	1200	400	Double	P2RA19S18	P2RA19T18	P2GARA4	N/A	N/A	P2AFB19
P2F18125	1800	1200	500	Double	P2RA19S18	P2RA19T18	P2GARA5	N/A	N/A	P2AFB19
P2F18126	1800	1200	600	Double	P2RA19S18	P2RA19T18	P2GARA6	N/A	N/A	P2AFB19
P2F18128	1800	1200	800	Double	P2RA19S18	P2RA19T18	P2GARA8	N/A	N/A	P2AFB19
P2F18164	1800	1600	400	Double	P2RA19S18	P2RA19T18	P2GARA4	N/A	N/A	P2AFB19
P2F18165	1800	1600	500	Double	P2RA19S18	P2RA19T18	P2GARA5	N/A	N/A	P2AFB19
P2F18166	1800	1600	600	Double	P2RA19S18	P2RA19T18	P2GARA6	N/A	N/A	P2AFB19
P2F18168	1800	1600	800	Double	P2RA19S18	P2RA19T18	P2GARA8	N/A	N/A	P2AFB19
P2F18185	1800	1800	500	Double	P2RA19S18	P2RA19T18	P2GARA5	N/A	N/A	P2AFB19
P2F18186	1800	1800	600	Double	P2RA19S18	P2RA19T18	P2GARA6	N/A	N/A	P2AFB19
P2F18188	1800	1800	800	Double	P2RA19S18	P2RA19T18	P2GARA8	N/A	N/A	P2AFB19
P2F2045	2000	400	500	Single	N/A	N/A	N/A	N/A	N/A	P2AFB19
P2F2046	2000	400	600	Single	N/A	N/A	N/A	N/A	N/A	P2AFB19
P2F2064	2000	600	400	Single	P2RA19S20	P2RA19T20	P2GARA4	N/A	N/A	P2AFB19
P2F2065	2000	600	500	Single	P2RA19S20	P2RA19T20	P2GARA5	N/A	N/A	P2AFB19
P2F2066	2000	600	600	Single	P2RA19S20	P2RA19T20	P2GARA6	N/A	N/A	P2AFB19
P2F2068	2000	600	800	Single	P2RA19S20	P2RA19T20	P2GARA8	N/A	N/A	P2AFB19
P2F2084	2000	800	400	Single	P2RA19S20	P2RA19T20	P2GARA4	P2AFRB100	P2AFRB200	P2AFB19
P2F2085	2000	800	500	Single	P2RA19S20	P2RA19T20	P2GARA5	P2AFRB100	P2AFRB200	P2AFB19
P2F2086	2000	800	600	Single	P2RA19S20	P2RA19T20	P2GARA6	P2AFRB100	P2AFRB200	P2AFB19
P2F2088	2000	800	800	Single	P2RA19S20	P2RA19T20	P2GARA8	P2AFRB100	P2AFRB200	P2AFB19
P2F20810	2000	800	1000	Single	P2RA19S20	P2RA19T20	P2GARA10	P2AFRB100	P2AFRB200	P2AFB19
P2F20105	2000	1000	500	Single	P2RA19S20	P2RA19T20	P2GARA5	P2AFRB200	N/A	P2AFB19
P2F20106	2000	1000	600	Single	P2RA19S20	P2RA19T20	P2GARA6	P2AFRB200	N/A	P2AFB19

										
Frame Catalog Number	H (mm)	W (mm)	D (mm)	Bay Count	19-inch Rack Angle (Square Hole)	19-inch Rack Angle (Tapped Hole)	Adjustable Rack-Mount Rails	Frame Reducing Bracket 19-inch Centered	Frame Reducing Bracket 19-inch Justified	Frame Accessory Bracket
P2F20108	2000	1000	800	Single	P2RA19S20	P2RA19T20	P2GARA8	P2AFRB200	N/A	P2AFB19
P2F20124	2000	1200	400	Double	P2RA19S20	P2RA19T20	P2GARA4	N/A	N/A	P2AFB19
P2F20125	2000	1200	500	Double	P2RA19S20	P2RA19T20	P2GARA5	N/A	N/A	P2AFB19
P2F20126	2000	1200	600	Double	P2RA19S20	P2RA19T20	P2GARA6	N/A	N/A	P2AFB19
P2F20128	2000	1200	800	Double	P2RA19S20	P2RA19T20	P2GARA8	N/A	N/A	P2AFB19
P2F20165	2000	1600	500	Double	P2RA19S20	P2RA19T20	P2GARA5	N/A	N/A	P2AFB19
P2F20166	2000	1600	600	Double	P2RA19S20	P2RA19T20	P2GARA6	N/A	N/A	P2AFB19
P2F20168	2000	1600	800	Double	P2RA19S20	P2RA19T20	P2GARA8	N/A	N/A	P2AFB19
P2F20185	2000	1800	500	Double	P2RA19S20	P2RA19T20	P2GARA5	N/A	N/A	P2AFB19
P2F20186	2000	1800	600	Double	P2RA19S20	P2RA19T20	P2GARA6	N/A	N/A	P2AFB19
P2F20188	2000	1800	800	Double	P2RA19S20	P2RA19T20	P2GARA8	N/A	N/A	P2AFB19
P2F2265	2200	600	500	Single	P2RA19S22	P2RA19T22	P2GARA5	N/A	N/A	P2AFB19
P2F2266	2200	600	600	Single	P2RA19S22	P2RA19T22	P2GARA6	N/A	N/A	P2AFB19
P2F2268	2200	600	800	Single	P2RA19S22	P2RA19T22	P2GARA8	N/A	N/A	P2AFB19
P2F2285	2200	800	500	Single	P2RA19S22	P2RA19T22	P2GARA5	P2AFRB100	P2AFRB200	P2AFB19
P2F2286	2200	800	600	Single	P2RA19S22	P2RA19T22	P2GARA6	P2AFRB100	P2AFRB200	P2AFB19
P2F2288	2200	800	800	Single	P2RA19S22	P2RA19T22	P2GARA8	P2AFRB100	P2AFRB200	P2AFB19
P2F22810	2200	800	1000	Single	P2RA19S22	P2RA19T22	P2GARA10	P2AFRB100	P2AFRB200	P2AFB19
P2F22105	2200	1000	500	Single	P2RA19S22	P2RA19T22	P2GARA5	P2AFRB200	N/A	P2AFB19
P2F22106	2200	1000	600	Single	P2RA19S22	P2RA19T22	P2GARA6	P2AFRB200	N/A	P2AFB19
P2F22108	2200	1000	800	Single	P2RA19S22	P2RA19T22	P2GARA8	P2AFRB200	N/A	P2AFB19
P2F22125	2200	1200	500	Double	P2RA19S22	P2RA19T22	P2GARA5	N/A	N/A	P2AFB19
P2F22126	2200	1200	600	Double	P2RA19S22	P2RA19T22	P2GARA6	N/A	N/A	P2AFB19
P2F22128	2200	1200	800	Double	P2RA19S22	P2RA19T22	P2GARA8	N/A	N/A	P2AFB19
P2F22165	2200	1600	500	Double	P2RA19S22	P2RA19T22	P2GARA5	N/A	N/A	P2AFB19
P2F22166	2200	1600	600	Double	P2RA19S22	P2RA19T22	P2GARA6	N/A	N/A	P2AFB19
P2F22168	2200	1600	800	Double	P2RA19S22	P2RA19T22	P2GARA8	N/A	N/A	P2AFB19
P2F22185	2200	1800	500	Double	P2RA19S22	P2RA19T22	P2GARA5	N/A	N/A	P2AFB19
P2F22186	2200	1800	600	Double	P2RA19S22	P2RA19T22	P2GARA6	N/A	N/A	P2AFB19
P2F22188	2200	1800	800	Double	P2RA19S22	P2RA19T22	P2GARA8	N/A	N/A	P2AFB19

Rack Accessories, 19-inch

Accessory	Fits Frame Depth (mm)	Fits Accessory	Rack Units Required
Drawer			
P19DR1US	600-1000		1U
P19DR2US	600-1000		2U
P19DR3US	600-1000		3U
Writing Surface			
P19WS		Drawer	
Pull-Out Shelf			
P19SHP68	600-1000		2U
P19SHP810	800-1000		2U
Screw Package			
AS1032		Rack Angles	
ASM5		Rack Angles	
Cage Nut Package			
P1032CN		Rack Angles	
PM5CN		Rack Angles	
Fixed Shelf			
P2RSH4	400-1000		1U
P2RSH5	500-1000		1U
P2RSH6	600-1000		1U
P2RSH8	800-1000		1U
P2RSH10	1000		1U
Guides			
P2RG4	400		1U
P2RG5	500		1U
P2RG5	600		1U
P2RG8	800		1U
P2RG10	1000		1U
Slides			
A16SL2U	600-1000		3U

Rack Accessories, 19-inch

Accessory	Fits Frame Depth (mm)	Fits Accessory	Rack Units Required
Rack Panels Aluminum			
P19RP1UA			1U
P19RP2UA			2U
P19RP3UA			3U
P19RP4UA			4U
P19RP5UA			5U
P19RP6UA			6U
P19RP7UA			7U
P19RP8UA			8U
P19RP9UA			9U
P19RP10UA			10U
P19RP11UA			11U
P19RP12UA			12U
P19RP16A			16U
Rack Panels, Painted Steel			
P19RP1UP			1U
P19RP2UP			2U
P19RP3UP			3U
P19RP4UP			4U
P19RP5UP			5U
P19RP6UP			6U
P19RP7UP			7U
P19RP8UP			8U
P19RP9UP			9U
P19RP10UP			10U
P19RP11UP			11U
P19RP12UP			12U
P19RP16UP			16U
Filler Panel			
PFP19RA		Rack Angles	
Keyboard Compartment			
A19KBC2			2U
Fan Tray			
A19FT3			1U
A19FT6			1U