

SELECTION MATRIX: DISCONNECT PACKAGES, TYPE 12

														
Frame	A	B	C	No. of Doors	Solid Disconnect Top	Solid Side Cover	Solid Rear Cover	Solid Disconnect Door (Left Mullion, Standard Cut-out)	Solid Disconnect Door (Right Mullion, Standard Cut-out)	Solid Disconnect Door (Right Mullion, Large Cut-out)	Solid Rear Door	Disconnect Gland Plate	Disconnect Plinth Base, 100mm	Disconnect Mounting Subpanel
P2F1684	1600	800	400	1	P2T84	P2CS164	P2C168	P2DDL168	P2DDR168	P2DDRL168	P2D168	P2BGP84G	P2BP184	P2P168G
P2F1685	1600	800	500	1	P2T85	P2CS165	P2C168	P2DDL168	P2DDR168	P2DDRL168	P2D168	P2BGP85G	P2BP185	P2P168G
P2F1686	1600	800	600	1	P2T86	P2CS166	P2C168	P2DDL168	P2DDR168	P2DDRL168	P2D168	P2BGP86G	P2BP186	P2P168G
P2F1688	1600	800	800	1	P2T88	P2CS168	P2C168	P2DDL168	P2DDR168	P2DDRL168	P2D168	P2BGP88G	P2BP188	P2P168G
P2F16104	1600	1000	400	1	P2T104	P2CS164	P2C1610	P2DDL1610	P2DDR1610	P2DDRL1610	N/A	P2BGP104G	P2BP1104	P2P1610G
P2F16106	1600	1000	600	1	P2T106	P2CS166	P2C1610	P2DDL1610	P2DDR1610	P2DDRL1610	N/A	P2BGP106G	P2BP1106	P2P1610G
P2FD16124	1600	1200	400	2	P2TD124	P2CS164	P2C1612	P2DDL1612	P2DDR1612	P2DDRL1612	P2D01612	P2BGPD124	P2BP1D124	P2PD1612G
P2FD16126	1600	1200	600	2	P2TD126	P2CS166	P2C1612	P2DDL1612	P2DDR1612	P2DDRL1612	P2D01612	P2BGPD126	P2BP1D126	P2PD1612G
P2FD16164	1600	1600	400	2	P2TD164	P2CS164	P2C168 (2)	P2DDL1616	P2DDR1616	P2DDRL1616	P2D01616	P2BGPD164	P2BP1D164	P2PD1616G
P2FD16166	1600	1600	600	2	P2TD166	P2CS166	P2C168 (2)	P2DDL1616	P2DDR1616	P2DDRL1616	P2D01616	P2BGPD166	P2BP1D166	P2PD1616G
P2F1884	1800	800	400	1	P2T84	P2CS184	P2C188	P2DDL188	P2DDR188	P2DDRL188	P2D188	P2BGP84G	P2BP184	P2P188G
P2F1885	1800	800	500	1	P2T85	P2CS185	P2C188	P2DDL188	P2DDR188	P2DDRL188	P2D188	P2BGP85G	P2BP185	P2P188G
P2F1886	1800	800	600	1	P2T86	P2CS186	P2C188	P2DDL188	P2DDR188	P2DDRL188	P2D188	P2BGP86G	P2BP186	P2P188G
P2F1888	1800	800	800	1	P2T88	P2CS188	P2C188	P2DDL188	P2DDR188	P2DDRL188	P2D188	P2BGP88G	P2BP188	P2P188G
P2F18104	1800	1000	400	1	P2T104	P2CS184	P2C1810	P2DDL1810	P2DDR1810	P2DDRL1810	P2D1810	P2BGP104G	P2BP1104	P2P1810G
P2F18105	1800	1000	500	1	P2T105	P2CS185	P2C1810	P2DDL1810	P2DDR1810	P2DDRL1810	P2D1810	P2BGP105G	P2BP1105	P2P1810G
P2F18106	1800	1000	600	1	P2T106	P2CS186	P2C1810	P2DDL1810	P2DDR1810	P2DDRL1810	P2D1810	P2BGP106G	P2BP1106	P2P1810G
P2F18108	1800	1000	800	1	P2T108	P2CS188	P2C1810	P2DDL1810	P2DDR1810	P2DDRL1810	P2D1810	P2BGP108G	P2BP1108	P2P1810G
P2FD18124	1800	1200	400	2	P2TD124	P2CS184	P2C1812	P2DDL1812	P2DDR1812	P2DDRL1812	P2D01812	P2BGPD124	P2BP1D124	P2PD1812G
P2FD18126	1800	1200	600	2	P2TD126	P2CS186	P2C1812	P2DDL1812	P2DDR1812	P2DDRL1812	P2D01812	P2BGPD126	P2BP1D126	P2PD1812G
P2FD18164	1800	1600	400	2	P2TD164	P2CS184	P2C188 (2)	P2DDL1816	P2DDR1816	P2DDRL1816	P2D01816	P2BGPD164	P2BP1D164	P2PD1816G
P2FD18166	1800	1600	600	2	P2TD166	P2CS186	P2C188 (2)	P2DDL1816	P2DDR1816	P2DDRL1816	P2D01816	P2BGPD166	P2BP1D166	P2PD1816G
P2FD18184	1800	1800	400	2	P2TD184	P2CS184	P2C189 (2)	P2DDL1818	P2DDR1818	P2DDRL1818	P2D01818	P2BGPD184	P2BP1D184	P2PD1818G
P2FD18186	1800	1800	600	2	P2TD186	P2CS186	P2C189 (2)	P2DDL1818	P2DDR1818	P2DDRL1818	P2D01818	P2BGPD186	P2BP1D186	P2PD1818G
P2F2084	2000	800	400	1	P2T84	P2CS204	P2C208	P2DDL208	P2DDR208	P2DDRL208	P2D208	P2BGP84G	P2BP184	P2P208G
P2F2085	2000	800	500	1	P2T85	P2CS205	P2C208	P2DDL208	P2DDR208	P2DDRL208	P2D208	P2BGP85G	P2BP185	P2P208G
P2F2086	2000	800	600	1	P2T86	P2CS206	P2C208	P2DDL208	P2DDR208	P2DDRL208	P2D208	P2BGP86G	P2BP186	P2P208G

														
Frame	A	B	C	No. of Doors	Solid Disconnect Top	Solid Side Cover	Solid Rear Cover	Solid Disconnect Door (Left Mullion, Standard Cut-out)	Solid Disconnect Door (Right Mullion, Standard Cut-out)	Solid Disconnect Door (Right Mullion, Large Cut-out)	Solid Rear Door	Disconnect Gland Plate	Disconnect Plinth Base, 100mm	Disconnect Mounting Subpanel
P2F2088	2000	800	800	1	P2T88	P2CS208	P2C208	P2DDL208	P2DDR208	P2DDR208	P2D208	P2BGP88G	P2BP188	P2P208G
P2F20810	2000	800	1000	1	P2T810	P2CS2010	P2C208	P2DDL208	P2DDR208	P2DDR208	P2D208	P2BGP810G	P2BP1810	P2P208G
P2F20104	2000	1000	400	1	P2T104	P2CS204	P2C2010	P2DDL2010	P2DDR2010	P2DDR2010	P2D2010	P2BGP104G	P2BP1104	P2P2010G
P2F20105	2000	1000	500	1	P2T105	P2CS205	P2C2010	P2DDL2010	P2DDR2010	P2DDR2010	P2D2010	P2BGP105G	P2BP1105	P2P2010G
P2F20106	2000	1000	600	1	P2T106	P2CS206	P2C2010	P2DDL2010	P2DDR2010	P2DDR2010	P2D2010	P2BGP106G	P2BP1106	P2P2010G
P2F20108	2000	1000	800	1	P2T108	P2CS208	P2C2010	P2DDL2010	P2DDR2010	P2DDR2010	P2D2010	P2BGP108G	P2BP1108	P2P2010G
P2FD20124	2000	1200	400	2	P2TD124	P2CS204	P2C2012	P2DDL2012	P2DDR2012	P2DDR2012	P2D02012	P2BGPD124	P2BP1D124	P2PD2012G
P2FD20126	2000	1200	600	2	P2TD126	P2CS206	P2C2012	P2DDL2012	P2DDR2012	P2DDR2012	P2D02012	P2BGPD126	P2BP1D126	P2PD2012G
P2FD20164	2000	1600	400	2	P2TD164	P2CS204	P2C208 (2)	P2DDL2016	P2DDR2016	P2DDR2016	P2D02016	P2BGPD164	P2BP1D164	P2PD2016G
P2FD20166	2000	1600	600	2	P2TD166	P2CS206	P2C208 (2)	P2DDL2016	P2DDR2016	P2DDR2016	P2D02016	P2BGPD166	P2BP1D166	P2PD2016G
P2FD20184	2000	1800	400	2	P2TD184	P2CS204	P2C209 (2)	P2DDL2018	P2DDR2018	P2DDR2018	P2D02018	P2BGPD184	P2BP1D184	P2PD2018G
P2FD20186	2000	1800	600	2	P2TD186	P2CS206	P2C209 (2)	P2DDL2018	P2DDR2018	P2DDR2018	P2D02018	P2BGPD186	P2BP1D186	P2PD2018G
P2F2285	2200	800	500	1	P2T85	P2CS225	P2C228	P2DDL228	P2DDR228	P2DDR228	P2D228	P2BGP85G	P2BP185	P2P228G
P2F2286	2200	800	600	1	P2T86	P2CS226	P2C228	P2DDL228	P2DDR228	P2DDR228	P2D228	P2BGP86G	P2BP186	P2P228G
P2F2288	2200	800	800	1	P2T88	P2CS228	P2C228	P2DDL228	P2DDR228	P2DDR228	P2D228	P2BGP88G	P2BP188	P2P228G
P2F22810	2200	800	1000	1	P2T810	P2CS2210	P2C228	P2DDL228	P2DDR228	P2DDR228	P2D228	P2BGP810G	P2BP1810	P2P228G
P2F22105	2200	1000	500	1	P2T105	P2CS225	P2C2210	P2DDL2210	P2DDR2210	P2DDR2210	P2D2210	P2BGP105G	P2BP1105	P2P2210G
P2F22106	2200	1000	600	1	P2T106	P2CS226	P2C2210	P2DDL2210	P2DDR2210	P2DDR2210	P2D2210	P2BGP106G	P2BP1106	P2P2210G
P2F22108	2200	1000	800	1	P2T108	P2CS228	P2C2210	P2DDL2210	P2DDR2210	P2DDR2210	P2D2210	P2BGP108G	P2BP1108	P2P2210G
P2FD22124	2200	1200	400	2	P2TD124	P2CS224	P2C2212	P2DDL2212	P2DDR2212	P2DDR2212	P2D02212	P2BGPD124	P2BP1D124	P2PD2212G
P2FD22126	2200	1200	600	2	P2TD126	P2CS226	P2C2212	P2DDL2212	P2DDR2212	P2DDR2212	P2D02212	P2BGPD126	P2BP1D126	P2PD2212G
P2FD22164	2200	1600	400	2	P2TD164	P2CS224	P2C228 (2)	P2DDL2216	P2DDR2216	P2DDR2216	P2D02216	P2BGPD164	P2BP1D164	P2PD2216G
P2FD22166	2200	1600	600	2	P2TD166	P2CS226	P2C228 (2)	P2DDL2216	P2DDR2216	P2DDR2216	P2D02216	P2BGPD166	P2BP1D166	P2PD2216G
P2FD22184	2200	1800	400	2	P2TD184	P2CS224	P2C229 (2)	P2DDL2218	P2DDR2218	P2DDR2218	P2D02218	P2BGPD184	P2BP1D184	P2PD2218G
P2FD22186	2200	1800	600	2	P2TD186	P2CS226	P2C229 (2)	P2DDL2218	P2DDR2218	P2DDR2218	P2D02218	P2BGPD186	P2BP1D186	P2PD2218G