

Universal Barrier Panel

PROTECT YOUR PERSONNEL AND EQUIPMENT FROM ELECTRICAL HAZARDS

SEPARATE HIGH AND LOW VOLTAGE COMPONENTS WITHIN AN ENCLOSURE

Want to access low voltage equipment such as controls and programming devices while power is on to reduce down time? The universal barrier panel creates a Type 1 rated barrier inside the enclosure to separate low and high voltage components. This reduces the risk of electrical shock or arc flash while accessing low voltage components by eliminating the hazard of high voltage contact given proper system design.














KEY FEATURES

- UL Type 1 rated when installed in an nVent HOFFMAN enclosure
- Finger safe (IP20)
- Full-depth separation; top and bottom barrier plates included
- Simple installation: secure the main barrier plate to the top barrier plate with quick release hinges
- Universal design that fits unibody, free-stand or floor-mount enclosures with centerpost
- Main barrier plate can be extended up to six inches to provide maximum separation and flexibility
- Option of white polyester powder paint or galvanized

PRODUCT SELECTION GUIDE

The Universal Barrier Panel can be installed in various nVent HOFFMAN free-stand or floor-mount enclosures with centerpost. Use the table below to help you identify which bulletin is compatible with the Universal Barrier Panel.

Mild Steel						
Enclosure Type	Two-Door with Floor Stands Disconnect Enclosure, Type 12	Heavy-Duty Free-Stand Disconnect Enclosure, Type 12	Free-Stand Disconnect with Quick-Release Hinge, Type 4	Two-Door with 3-Point Latches and Floor Stands, Type 4	Two-Door with Floor Stands, Type 4	
Bulletin	A21	A28M2, A28MM	A4L3D	A4L3	A4L	
Image						
Note	Will not work on CPX enclosures					

Stainless Steel						
Enclosure Type	Two-Door Enclosures for Flange-Mounted Disconnects, Type 4X	Heavy-Duty Free-Stand Enclosures for Flange-Mount Disconnects, Type 4X	General Purpose Two-Door Floor-Mount Disconnect Enclosures, Type 4X	General Purpose Two-Door with Quarter-Turn Latches and Floor Stands, Type 4X	Two-Door with 3-Point Latches, Type 4X	Two-Door with Floor Stands, Type 4X
Bulletin	A21S4	A28S4	A4S2	A4S2	A4S3	A4SL
Image						
Note	Will not work on CPX enclosures					



Our powerful portfolio of brands:

nVent.com

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER