
























## SELECTION MATRIX: DOORS, COVERS AND SIDES

												
Frame	A	B	C	Solid Side	Solid Cover	Solid Single Door	Overlapping Solid Doors	Polycarbonate Window Door	Safety Glass Window Door	Overlapping Safety Glass Window Door	Overlapping Polycarbonate Window Door	Dress Frame
P2F664	600	600	400	P2CS64	P2C66	P2D66	N/A	P2DW66	P2DWG66	N/A	N/A	P2DF66
P2F666	600	600	600	P2CS66	P2C66	P2D66	N/A	P2DW66	P2DWG66	N/A	N/A	P2DF66
P2F688	600	800	800	P2CS68	P2C68	P2D68	P2D068	P2DW68	P2DWG68	N/A	N/A	P2DF68
P2F864	800	600	400	P2CS84	P2C86	P2D86	N/A	P2DW86	P2DWG86	N/A	N/A	P2DF86
P2F866	800	600	600	P2CS86	P2C86	P2D86	N/A	P2DW86	P2DWG86	N/A	N/A	P2DF86
P2F888	800	800	800	P2CS88	P2C88	P2D88	P2D088	P2DW88	P2DWG88	N/A	N/A	P2DF88
P2F1064	1000	600	400	P2CS104	P2C106	P2D106	N/A	P2DW106	P2DWG106	N/A	N/A	P2DF106
P2F1065	1000	600	500	P2CS105	P2C106	P2D106	N/A	P2DW106	P2DWG106	N/A	N/A	P2DF106
P2F1066	1000	600	600	P2CS106	P2C106	P2D106	N/A	P2DW106	P2DWG106	N/A	N/A	P2DF106
P2F1085	1000	800	500	P2CS105	P2C108	P2D108	P2D0108	P2DW108	P2DWG108	N/A	N/A	P2DF108
P2F1086	1000	800	600	P2CS106	P2C108	P2D108	P2D0108	P2DW108	P2DWG108	N/A	N/A	P2DF108
P2F1088	1000	800	800	P2CS108	P2C108	P2D108	P2D0108	P2DW108	P2DWG108	N/A	N/A	P2DF108
P2F10125	1000	1200	500	P2CS105	P2C1012	N/A	P2D01012	N/A	N/A	P2DWOG1012	P2DW01012	N/A
P2F1264	1200	600	400	P2CS124	P2C126	P2D126	N/A	P2DW126	P2DWG126	N/A	N/A	P2DF126
P2F1265	1200	600	500	P2CS125	P2C126	P2D126	N/A	P2DW126	P2DWG126	N/A	N/A	P2DF126
P2F1266	1200	600	600	P2CS126	P2C126	P2D126	N/A	P2DW126	P2DWG126	N/A	N/A	P2DF126
P2F1285	1200	800	500	P2CS125	P2C128	P2D128	P2D0128	P2DW128	P2DWG128	N/A	N/A	P2DF128
P2F1286	1200	800	600	P2CS126	P2C128	P2D128	P2D0128	P2DW128	P2DWG128	N/A	N/A	P2DF128
P2F1288	1200	800	800	P2CS128	P2C128	P2D128	P2D0128	P2DW128	P2DWG128	N/A	N/A	P2DF128
P2F12125	1200	1200	500	P2CS125	P2C1212	N/A	P2D01212	N/A	N/A	P2DWOG1212	P2DW01212	N/A
P2F1465	1400	600	500	P2CS145	P2C146	P2D146	N/A	P2DW146	P2DWG146	N/A	N/A	P2DF146
P2F1466	1400	600	600	P2CS146	P2C146	P2D146	N/A	P2DW146	P2DWG146	N/A	N/A	P2DF146
P2F1468	1400	600	800	P2CS148	P2C146	P2D146	N/A	P2DW146	P2DWG146	N/A	N/A	P2DF146
P2F1485	1400	800	500	P2CS145	P2C148	P2D148	P2D0148	P2DW148	P2DWG148	N/A	N/A	P2DF148
P2F1486	1400	800	600	P2CS146	P2C148	P2D148	P2D0148	P2DW148	P2DWG148	N/A	N/A	P2DF148
P2F1488	1400	800	800	P2CS148	P2C148	P2D148	P2D0148	P2DW148	P2DWG148	N/A	N/A	P2DF148
P2F14125	1400	1200	500	P2CS145	P2C1412	N/A	P2D01412	N/A	N/A	P2DWOG1412	P2DW01412	N/A
P2F1664	1600	600	400	P2CS164	P2C166	P2D166	N/A	P2DW166	P2DWG166	N/A	N/A	P2DF166
P2F1665	1600	600	500	P2CS165	P2C166	P2D166	N/A	P2DW166	P2DWG166	N/A	N/A	P2DF166
P2F1666	1600	600	600	P2CS166	P2C166	P2D166	N/A	P2DW166	P2DWG166	N/A	N/A	P2DF166
P2F1668	1600	600	800	P2CS168	P2C166	P2D166	N/A	P2DW166	P2DWG166	N/A	N/A	P2DF166
P2F1684	1600	800	400	P2CS164	P2C168	P2D168	P2D0168	P2DW168	P2DWG168	N/A	N/A	P2DF168
P2F1685	1600	800	500	P2CS165	P2C168	P2D168	P2D0168	P2DW168	P2DWG168	N/A	N/A	P2DF168
P2F1686	1600	800	600	P2CS166	P2C168	P2D168	P2D0168	P2DW168	P2DWG168	N/A	N/A	P2DF168
P2F1688	1600	800	800	P2CS168	P2C168	P2D168	P2D0168	P2DW168	P2DWG168	N/A	N/A	P2DF168
P2F16104	1600	1000	400	P2CS164	P2C1610	N/A	N/A	N/A	N/A	N/A	N/A	N/A
P2F16106	1600	1000	600	P2CS166	P2C1610	N/A	N/A	N/A	N/A	N/A	N/A	N/A
P2F16124	1600	1200	400	P2CS164	P2C1612	N/A	P2D01612	N/A	N/A	P2DWOG1612	P2DW01612	N/A
P2F16125	1600	1200	500	P2CS165	P2C1612	N/A	P2D01612	N/A	N/A	P2DWOG1612	P2DW01612	N/A
P2F16126	1600	1200	600	P2CS166	P2C1612	N/A	P2D01612	N/A	N/A	P2DWOG1612	P2DW01612	N/A

 				 		 						
Frame	A	B	C	Solid Side	Solid Cover	Solid Single Door	Overlapping Solid Doors	Polycarbonate Window Door	Safety Glass Window Door	Overlapping Safety Glass Window Door	Overlapping Polycarbonate Window Door	Dress Frame
P2F16128	1600	1200	800	P2CS168	P2C1612	N/A	P2D01612	N/A	N/A	P2DWOG1612	P2DWO1612	N/A
P2F16164	1600	1600	400	P2CS164	P2C168 (2)	N/A	P2D01616	N/A	N/A	P2DWOG1616	P2DWO1616	N/A
P2F16165	1600	1600	500	P2CS165	P2C168 (2)	N/A	P2D01616	N/A	N/A	P2DWOG1616	P2DWO1616	N/A
P2F16166	1600	1600	600	P2CS166	P2C168 (2)	N/A	P2D01616	N/A	N/A	P2DWOG1616	P2DWO1616	N/A
P2F16168	1600	1600	800	P2CS168	P2C168 (2)	N/A	P2D01616	N/A	N/A	P2DWOG1616	P2DWO1616	N/A
P2F1845	1800	400	500	P2CS185	P2C184	P2D184	N/A	P2DW184	P2DWG184	N/A	N/A	P2DF184
P2F1846	1800	400	600	P2CS186	P2C184	P2D184	N/A	P2DW184	P2DWG184	N/A	N/A	P2DF184
P2F1864	1800	600	400	P2CS184	P2C186	P2D186	N/A	P2DW186	P2DWG186	N/A	N/A	P2DF186
P2F1865	1800	600	500	P2CS185	P2C186	P2D186	N/A	P2DW186	P2DWG186	N/A	N/A	P2DF186
P2F1866	1800	600	600	P2CS186	P2C186	P2D186	N/A	P2DW186	P2DWG186	N/A	N/A	P2DF186
P2F1868	1800	600	800	P2CS188	P2C186	P2D186	N/A	P2DW186	P2DWG186	N/A	N/A	P2DF186
P2F1884	1800	800	400	P2CS184	P2C188	P2D188	P2D0188	P2DW188	P2DWG188	N/A	N/A	P2DF188
P2F1885	1800	800	500	P2CS185	P2C188	P2D188	P2D0188	P2DW188	P2DWG188	N/A	N/A	P2DF188
P2F1886	1800	800	600	P2CS186	P2C188	P2D188	P2D0188	P2DW188	P2DWG188	N/A	N/A	P2DF188
P2F1888	1800	800	800	P2CS188	P2C188	P2D188	P2D0188	P2DW188	P2DWG188	N/A	N/A	P2DF188
P2F18104	1800	1000	400	P2CS184	P2C1810	P2D1810	P2D01810	P2DW1810	P2DWG1810	N/A	N/A	N/A
P2F18105	1800	1000	500	P2CS185	P2C1810	P2D1810	P2D01810	P2DW1810	P2DWG1810	N/A	N/A	N/A
P2F18106	1800	1000	600	P2CS186	P2C1810	P2D1810	P2D01810	P2DW1810	P2DWG1810	N/A	N/A	N/A
P2F18108	1800	1000	800	P2CS188	P2C1810	P2D1810	P2D01810	P2DW1810	P2DWG1810	N/A	N/A	N/A
P2F18124	1800	1200	400	P2CS184	P2C1812	N/A	P2D01812	N/A	N/A	P2DWOG1812	P2DWO1812	N/A
P2F18125	1800	1200	500	P2CS185	P2C1812	N/A	P2D01812	N/A	N/A	P2DWOG1812	P2DWO1812	N/A
P2F18126	1800	1200	600	P2CS186	P2C1812	N/A	P2D01812	N/A	N/A	P2DWOG1812	P2DWO1812	N/A
P2F18128	1800	1200	800	P2CS188	P2C1812	N/A	P2D01812	N/A	N/A	P2DWOG1812	P2DWO1812	N/A
P2F18164	1800	1600	400	P2CS184	P2C188 (2)	N/A	P2D01816	N/A	N/A	P2DWOG1816	P2DWO1816	N/A
P2F18165	1800	1600	500	P2CS185	P2C188 (2)	N/A	P2D01816	N/A	N/A	P2DWOG1816	P2DWO1816	N/A
P2F18166	1800	1600	600	P2CS186	P2C188 (2)	N/A	P2D01816	N/A	N/A	P2DWOG1816	P2DWO1816	N/A
P2F18168	1800	1600	800	P2CS188	P2C188 (2)	N/A	P2D01816	N/A	N/A	P2DWOG1816	P2DWO1816	N/A
P2F18185	1800	1800	500	P2CS185	P2C189 (2)	N/A	P2D01818	N/A	N/A	P2DWOG1818	P2DWO1818	N/A
P2F18186	1800	1800	600	P2CS186	P2C189 (2)	N/A	P2D01818	N/A	N/A	P2DWOG1818	P2DWO1818	N/A
P2F18188	1800	1800	800	P2CS188	P2C189 (2)	N/A	P2D01818	N/A	N/A	P2DWOG1818	P2DWO1818	N/A
P2F2045	2000	400	500	P2CS205	P2C204	P2D204	N/A	P2DW204	P2DWG204	N/A	N/A	P2DF204
P2F2046	2000	400	600	P2CS206	P2C204	P2D204	N/A	P2DW204	P2DWG204	N/A	N/A	P2DF204
P2F2064	2000	600	400	P2CS204	P2C206	P2D206	N/A	P2DW206	P2DWG206	N/A	N/A	P2DF206
P2F2065	2000	600	500	P2CS205	P2C206	P2D206	N/A	P2DW206	P2DWG206	N/A	N/A	P2DF206
P2F2066	2000	600	600	P2CS206	P2C206	P2D206	N/A	P2DW206	P2DWG206	N/A	N/A	P2DF206
P2F2068	2000	600	800	P2CS208	P2C206	P2D206	N/A	P2DW206	P2DWG206	N/A	N/A	P2DF206
P2F2084	2000	800	400	P2CS204	P2C208	P2D208	P2D0208	P2DW208	P2DWG208	N/A	N/A	P2DF208
P2F2085	2000	800	500	P2CS205	P2C208	P2D208	P2D0208	P2DW208	P2DWG208	N/A	N/A	P2DF208
P2F2086	2000	800	600	P2CS206	P2C208	P2D208	P2D0208	P2DW208	P2DWG208	N/A	N/A	P2DF208
P2F2088	2000	800	800	P2CS208	P2C208	P2D208	P2D0208	P2DW208	P2DWG208	N/A	N/A	P2DF208
P2F20810	2000	800	1000	P2CS2010	P2C208	P2D208	P2D0208	P2DW208	P2DWG208	N/A	N/A	P2DF208
P2F20105	2000	1000	500	P2CS205	P2C2010	P2D2010	P2D02010	P2DW2010	P2DWG2010	N/A	N/A	N/A
P2F20106	2000	1000	600	P2CS206	P2C2010	P2D2010	P2D02010	P2DW2010	P2DWG2010	N/A	N/A	N/A

																
Frame	A	B	C	Solid Side	Solid Cover	Solid Single Door	Overlapping Solid Doors	Polycarbonate Window Door	Safety Glass Window Door	Overlapping Safety Glass Window Door	Overlapping Polycarbonate Window Door	Dress Frame				
P2F20108	2000	1000	800	P2CS208	P2C2010	P2D2010	P2D02010	P2DW2010	P2DWG2010	N/A	N/A	N/A				
P2F20124	2000	1200	400	P2CS204	P2C2012	N/A	P2D02012	N/A	N/A	P2DWOG2012	P2DWO2012	N/A				
P2F20125	2000	1200	500	P2CS205	P2C2012	N/A	P2D02012	N/A	N/A	P2DWOG2012	P2DWO2012	N/A				
P2F20126	2000	1200	600	P2CS206	P2C2012	N/A	P2D02012	N/A	N/A	P2DWOG2012	P2DWO2012	N/A				
P2F20128	2000	1200	800	P2CS208	P2C2012	N/A	P2D02012	N/A	N/A	P2DWOG2012	P2DWO2012	N/A				
P2F20165	2000	1600	500	P2CS205	P2C208 (2)	N/A	P2D02016	N/A	N/A	P2DWOG2016	P2DWO2016	N/A				
P2F20166	2000	1600	600	P2CS206	P2C208 (2)	N/A	P2D02016	N/A	N/A	P2DWOG2016	P2DWO2016	N/A				
P2F20168	2000	1600	800	P2CS208	P2C208 (2)	N/A	P2D02016	N/A	N/A	P2DWOG2016	P2DWO2016	N/A				
P2F20185	2000	1800	500	P2CS206	P2C209 (2)	N/A	P2D02018	N/A	N/A	P2DWOG2018	P2DWO2018	N/A				
P2F20186	2000	1800	600	P2CS208	P2C209 (2)	N/A	P2D02018	N/A	N/A	P2DWOG2018	P2DWO2018	N/A				
P2F20188	2000	1800	800	P2CS208	P2C209 (2)	N/A	P2D02018	N/A	N/A	P2DWOG2018	P2DWO2018	N/A				
P2F2265	2200	600	500	P2CS225	P2C225	P2D226	N/A	P2DW226	P2DWG226	N/A	N/A	P2DF226				
P2F2266	2200	600	600	P2CS226	P2C226	P2D226	N/A	P2DW226	P2DWG226	N/A	N/A	P2DF226				
P2F2268	2200	600	800	P2CS228	P2C226	P2D226	N/A	P2DW226	P2DWG226	N/A	N/A	P2DF226				
P2F2285	2200	800	500	P2CS225	P2C228	P2D228	P2D0228	P2DW228	P2DWG228	N/A	N/A	P2DF228				
P2F2286	2200	800	600	P2CS226	P2C228	P2D228	P2D0228	P2DW228	P2DWG228	N/A	N/A	P2DF228				
P2F2288	2200	800	800	P2CS228	P2C228	P2D228	P2D0228	P2DW228	P2DWG228	N/A	N/A	P2DF228				
P2F22810	2200	800	1000	P2CS2210	P2C228	P2D228	P2D0228	P2DW228	P2DWG228	N/A	N/A	P2DF228				
P2F22105	2200	1000	500	P2CS225	P2C2210	P2D2210	P2D02210	P2DW2210	P2DWG2210	N/A	N/A	N/A				
P2F22106	2200	1000	600	P2CS226	P2C2210	P2D2210	P2D02210	P2DW2210	P2DWG2210	N/A	N/A	N/A				
P2F22108	2200	1000	800	P2CS228	P2C2210	P2D2210	P2D02210	P2DW2210	P2DWG2210	N/A	N/A	N/A				
P2F22125	2200	1200	500	P2CS225	P2C2212	N/A	P2D02212	N/A	N/A	P2DWOG2212	P2DWO2212	N/A				
P2F22126	2200	1200	600	P2CS226	P2C2212	N/A	P2D02212	N/A	N/A	P2DWOG2212	P2DWO2212	N/A				
P2F22128	2200	1200	800	P2CS228	P2C2212	N/A	P2D02212	N/A	N/A	P2DWOG2212	P2DWO2212	N/A				
P2F22165	2200	1600	500	P2CS225	P2C228 (2)	N/A	P2D02216	N/A	N/A	P2DWOG2216	P2DWO2216	N/A				
P2F22166	2200	1600	600	P2CS226	P2C228 (2)	N/A	P2D02216	N/A	N/A	P2DWOG2216	P2DWO2216	N/A				
P2F22168	2200	1600	800	P2CS228	P2C228 (2)	N/A	P2D02216	N/A	N/A	P2DWOG2216	P2DWO2216	N/A				
P2F22185	2200	1800	500	P2CS225	P2C229 (2)	N/A	P2D02218	N/A	N/A	P2DWOG2218	P2DWO2218	N/A				
P2F22186	2200	1800	600	P2CS226	P2C229 (2)	N/A	P2D02218	N/A	N/A	P2DWOG2218	P2DWO2218	N/A				
P2F22188	2200	1800	800	P2CS228	P2C229 (2)	N/A	P2D02218	N/A	N/A	P2DWOG2218	P2DWO2218	N/A				