

LIGHT DUTY SUPPORT ARM SYSTEM FOR INDUSTRIAL APPLICATIONS

The Syspend 180-MAX is a modular enclosure suspension system designed for modern industrial aesthetics, excellent ergonomics and multiple component combinations.

The easy-to-install components can be configured in a variety of ways to get the right combination for any application.

At 3.3 ft. (1 m) the system supports up to 180 lbs. (81.6 kg). Recommended for use with CC2000, CC4000, and Concept HMI enclosures.



KEY FEATURES:

- Multiple modular components available to provide ergonomic, fatigue-free operation
- Six standard tube lengths offer system design versatility
- Tubes and couplings are wide enough to be DVI connector compatible
- Heavy-duty bearings in all movable joints for convenient, smooth operation and enhanced durability to withstand the stresses of repeated use
- Panel couplings allow for connection at the rear of displays or monitors with VESA mounting
- System supports up to 180 lbs. and allows operators to easily move controls in and out of position
- System can be combined with the Syspend 281-MAX using the Reduction Elbow to achieve a higher load rating

APPLICATIONS INCLUDE:

- Automotive
- Packaging
- Machine Building
- Oil and Gas

ASSEMBLE WITH EASE

Syspend 180-MAX benefits from an intelligent design that simplifies the installation process, making the system as easy to use as it is sleek and attractive.



Clean lines and smooth transitions between tubes and components provide modern aesthetics.



Secure attachment with six set screws connecting tubes to couplings.



System design can be assembled, re-adjusted or leveled by one worker without any additional tools or kits.

For more information visit nVent.com/HOFFMAN

North America

Minneapolis, MN
Tel: +1.763.421.2240
Mexico City, Mexico
Tel: +52.55.5280.1449
Toronto, Canada
Tel: +1.416.289.2770

South America

Sao Paulo, Brazil
Tel: +55.11.5184.2100
Boitura, Brazil
Tel: +55.15.3363.9148

Europe

Betschdorf, France
Tel: +33.3.88.90.64.90
Straubenhardt, Germany
Tel: +49.7082.794.0
Dzierzoniow, Poland
Tel: +48.74.64.63.900
Assago, Italy
Tel: +39.02.5776151.224

Middle East & India

Dubai, United Arab
Emirates
Tel: +971.4.378.1700
Bangalore, India
Tel: +91.80.6715.2001

Asia

Shanghai, P.R. China
Tel: +86.21.2412.6943
Singapur
Tel: +65.6768.5800
Shin-Yokohama, Japan
Tel: +81.45.476.0271
Seoul, Korea
Tel: +82.2.2129.7755
Qingdao
Tel: +86.532.8771.6101



nVent.com

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER