

## Declaration of Conformity

Issued by Manufacturer  
Hoffman Enclosures, Inc.  
2100 Hoffman Way, Anoka, Minnesota 55303-1745, U.S.A.  
declare at our sole responsibility, that these devices are designed and constructed according to  
the fundamental safety and health requirements.

**Enclosure Models:** PTDDCx (Bulletin P20DC)  
**Equipment Description:** Hoffman Proline-Disconnect Package, Type 12  
**Enclosure Rating:** CSA Type 12  
**Enclosure Certification:** CSA C22.2 No. 14 - 13

### PRODUCTS

CLASS - C321107 - INDUSTRIAL CONTROL EQUIPMENT-Miscellaneous Apparatus

CLASS - C321187 - INDUSTRIAL CONTROL EQUIPMENT-Miscellaneous Apparatus - Certified to US Standards

Industrial metal sheet enclosures, PROLINE Series, single door, CSA Type 12 max dimensions 2200 x 1000 x 800 mm, CSA Type 3R, 4, max dimensions 2200 x 800 x 800 mm; double door, CSA Type 12/3R, max dimensions 2200 x 1800 x 800; PC enclosure CSA Type 12, max dimensions 2000 x 800 x 800 mm; SY enclosure, CSA Type 12, max dimensions 1600 x 800 x 800 mm, with the following accessories: disconnect door, polycarbonate window door, window door safety glass, gland plate.

**Applicable Standards:** CSA C22.2 No. 14 - 13 – Industrial Control Equipment  
CAN/CSA C22.2 No. 94-M91 – Special Purpose Enclosures  
ANSI/UL 50 (11<sup>th</sup> edition) – Enclosures for Electrical Equipment  
ANSI/UL 508 (13<sup>th</sup> edition) – Industrial Control Equipment

Authorized by:



5/22/2020 (today's date)

**Glen Kampa**

**Date**

Senior Regulatory Engineer

Subject to Change Without Notice

DOC: CERT-00302-B

