

## Automatic transfer switch

unit : mm



Front view



Rear view



Top View



### Automatic transfer switch

Input Rating	: 20A, 208V
Outlet	: 10A Rated C13 x 12
Inlet	: 20A NEMA L6-20P plug x 2
Cordset	: 3 meter UL SJT 12 AWG cordset x 2
Protection	: 20A single pole hydraulic MCB x 1
Circuit Details	: Output 16A max. C13 #1-12

### ATS Specification :

Nominal input voltage	: 208V
Acceptable input voltage	: ±10% nominal
Input frequency	: 50 / 60Hz
Transfer time	: 10 ms typical
Electrical endurance	: 1 x 10 <sup>5</sup> operations
Power consumption	: Approx. 20W

### Meter Features ( WS - Outlet Switched )

Local Display	: 2.0" color LCD with touchscreen
Bank Measurement	: Current ( A ), Energy ( kWh ), Voltage ( V ) & Power factor
Outlet Control	: Outlet Switch ON / OFF
Accuracy	: ±1% Billing-grade
SNMP	: V2 / V3 version, via built-in IP dongle

Operating Temperature	: -5 to 60 °C
Storage Temperature	: -25 to 65 °C
Operating Altitude	: 0 to 2,000 m
Storage Altitude	: 0 to 15,000 m
Humidity	: 8 to 95% RH, non-condensing

EMC Compliance	: FCC Part 15 Subpart B
Safety Compliance	: TUVus to UL 60950-1:2007/R:2014-10 CAN/CSA-C22.2 No. 60950-1:2007/A2:2014-10

	: UL 62368-1:2014 CAN/CSA-C22.2 No. 62368-1:2014
--	---

	: UL 60730-1 Ed.5 (2016)
--	--------------------------

Environment Compliance	: RoHS2 & REACH
------------------------	-----------------

Dimension	: 17.2 (W) x 17.7 (D) x 1.7 (H) inch
-----------	--------------------------------------

Material	: Steel
----------	---------

Color	: Black
-------	---------