

## RACKPOWER AUTOMATIC TRANSFER SWITCH



### INDUSTRY STANDARDS

CE / EMC Certified  
LVD Certified  
9001 / 14001 Certified  
RoHS3 and REACH Compliant

### APPLICATION

The Rack Automatic Transfer Switches provide power redundancy to rack-mount IT devices that are not designed to take advantage of data centers' second power source. The ATS devices provide power failover for single-corded devices.

### FEATURES

- Provides power redundancy to single-corded IT devices, ensuring there is no downtime that could be caused by power interruptions
- Devices automatically and seamlessly switch power sources when power loss is detected from the primary input
- Power inputs can be switched at the rack on the ATS itself or remotely over IP, saving time and resources
- Power metrics can be monitored remotely over IP to assist with capacity planning and improve overall efficiency
- Provide remote on/off outlet switching over network IP
- Free management software provided to remotely manage the ATS
- All units include monitoring, circuit monitoring and outlet switching
- Local meter is field replaceable 2.00 (51mm) color LCD
- Overload protection: Hydraulic-magnetic Miniature Circuit Breaker (MCB)
- Transfer time: 10ms
- Operating temperature: 23-140 F (-5-60 C)
- Operating humidity: 0~95%, non-condensing

Catalog Number	Height in./mm	Width in./mm	Depth in./mm	Material	Finish	Color	Nominal Voltage (V)	Frequency (Hz)	Load Rating (A)	Receptacle Quantity	Receptacle Style	Power Cord Plug	Cord Length (ft.)	Cord Length (m)	Rack Unit Quantity
NPATS11001	1.71 44	17.72 450	17.40 442	Mild Steel	Powder Coated	Jet Black	110	50/60	15	10	10x NEMA	L515	10	3	1U
NPATS11002	1.71 44	17.72 450	17.40 442	Mild Steel	Powder Coated	Jet Black	110	50/60	20	10	10x NEMA	L520	10	3	1U
NPATS11003	3.46 88	17.72 450	17.40 442	Mild Steel	Powder Coated	Jet Black	110	50/60	20	16	10x NEMA	L520	10	3	2U
NPATS20801	1.71 44	17.72 450	17.40 442	Mild Steel	Powder Coated	Jet Black	208	50/60	20	12	12x C13	L620	10	3	1U
NPATS20802	1.71 44	17.72 450	17.40 442	Mild Steel	Powder Coated	Jet Black	208	50/60	20	9	8x C13, 1x C19	L620	10	3	1U
NPATS20803	3.46 88	17.72 450	17.40 442	Mild Steel	Powder Coated	Jet Black	208	50/60	30	1	1x L630R	L630	10	3	2U
NPATS20804	3.46 88	17.72 450	17.40 442	Mild Steel	Powder Coated	Jet Black	208	50/60	30	18	16x C13, 2x C19	L630	10	3	2U