

## Automatic transfer switch

unit : mm

Front view




44.5


Rear view



Top View



450



### Automatic transfer switch

Input Rating : 20A, 208V  
 Outlet : 10A Rated C13 x 8  
 16A Rated C19 x 1  
 Inlet : 20A NEMA L6-20P plug x 2  
 Cordset : 3 meter UL SJT 12 AWG cordset x 2  
 Protection : 20A single pole hydraulic MCB x 1  
 Circuit Details : Output 16A max. C13 #1-8 + C19 #C1

### ATS Specification :

Nominal input voltage : 208V  
 Acceptable input voltage :  $\pm 10\%$  nominal  
 Input frequency : 50 / 60Hz  
 Transfer time : 10 ms typical  
 Electrical endurance :  $1 \times 10^5$  operations  
 Power consumption : Approx. 20W

### Meter Features ( WS - Outlet Switched )

Local Display : 2.0" color LCD with touchscreen  
 Bank Measurement : Current ( A ), Energy ( kWh ), Voltage ( V ) & Power factor  
 Outlet Control : Outlet Switch ON / OFF  
 Accuracy :  $\pm 1\%$  Billing-grade  
 SNMP : V2 / V3 version, via built-in IP dongle  
 Operating Temperature : -5 to 60 °C  
 Storage Temperature : -25 to 65 °C  
 Operating Altitude : 0 to 2,000 m  
 Storage Altitude : 0 to 15,000 m  
 Humidity : 8 to 95% RH, non-condensing

EMC Compliance : FCC Part 15 Subpart B  
 Safety Compliance : TUVus to UL 60950-1:2007/R:2014-10  
 CAN/CSA-C22.2 No. 60950-1:2007/A2:2014-10  
 UL 62368-1:2014  
 CAN/CSA-C22.2 No. 62368-1:2014  
 UL 60730-1 Ed.5 (2016)  
 Environment Compliance : RoHS2 & REACH  
 Dimension : 17.2 (W) x 17.7 (D) x 1.7 (H) inch  
 Material : Steel  
 Color : Black