

CURRENT TRANSFORMER CABINET, LOUISIANA, TYPE 3R



INDUSTRY STANDARDS

UL 414 Listed; Type 3R; File No. E240312
 UL 50, 50E Listed; Type 3R; File No. E27525
 cUL Listed per CSA C22.2 No 94; Type 3R; File No. E27525

NEMA Type 3R
 IEC 60529, IP32

APPLICATION

The cabinets provide outdoor protection and security for instrument current transformers, which are frequently required for transformer-rated watt-hour metering. This cabinet can also be used as junction or service boxes and house meter, transformer, relay or terminal assemblies. It offers the flexibility of mounting instrument current transformer vertically or horizontally.

FEATURES

- Provisions for padlocking on draw-pull catch
- Welded hinge and pin for non-removable door
- Includes 12 gauge painted steel panel
- Drip shield top and seam-free sides
- Includes optional handle kit
- Embossed mounting holes on back of enclosure
- Grounding provisions on door and body
- No knockouts

SPECIFICATIONS

- 14 gauge galvanized steel

FINISH

ANSI 61 gray polyester powder coated paint inside and out over pretreated surfaces.

ACCESSORIES

- Industrial Corrosion Inhibitors
- Grounding Device
- Touch-Up Paint

Catalog Number	AxBxC in./mm	D in./mm	E in./mm
A242410CTLAE	24.00 x 24.00 x 10.00 610 x 610 x 254	19.81 503	20.81 529
A363010CTLAE	36.00 x 30.00 x 10.00 914 x 762 x 254	25.81 656	32.81 833
A403214CTLAE	40.00 x 32.00 x 14.00 1016 x 813 x 356	27.81 706	36.81 935
A543214CTLAE	54.00 x 32.00 x 14.00 1372 x 813 x 356	27.81 706	50.81 1291

