

ProTek Wall-Mount Enclosures



HOFFMAN

RUGGED AND FLEXIBLE ENCLOSURES FOR NETWORKING APPLICATIONS

SPACE-EFFICIENT PROTECTION FOR DISTRIBUTED NETWORKS

The need for robust and space-saving cabinets to protect, house and cool remote sensitive electronic and electrical components is essential and critical for any application.

ProTek is an excellent choice for applications where space is at a premium and the only option is wall mounting. ProTek is available in a broad range of sizes, materials and configurations to meet many demanding applications.

The expanded ProTek line offers the most versatile and rugged solution for IDF and other electronic applications indoors and out—including protection, thermal management and easy access to rack-mounted, 19-in. (483 mm) panel and other sensitive electronics.



KEY FEATURES

- **Complete, off-the-shelf packages** with one part number to meet application needs
- **Versatile configurations** in single-door and high-accessibility double-hinged door models
- **Plated, adjustable RU marked** for 19-in. (483 mm) EIA rack mounting
- **NEMA ratings** Type 12, 3R, 4 and 4X
- **Latching** -1/4-turn keylocking or 1/4-slotted latch
- **Variety of materials** to suit specific application requirements
- **Integral cooling** with low-profile fan and A/C packages
- **Load capacity** ranging from 175 lbs to 400 lbs (79 to 181 kg) depending on enclosure size
- **Size range:** 16 x 24 x 15 to 60 x 24 x 15 in. (406 x 610 x 381 to 1524 x 610 x 381 mm)

APPLICATIONS INCLUDE:

- Distributed control
- Enterprise communications
- Intermediate distribution frames
- 19-in. (483 mm) rack mounted instruments
- Factory and building automation
- Security (cameras, access control, recordings)
- Retail roll-outs
- DAS/Small cell
- Telecommunications

ProTek Wall-Mount Enclosures

EXTREME PROTECTION FOR PUNISHING ENVIRONMENTS

ProTek cabinets offer robust protection against water, dirt, corrosive agents and other contaminants, as well as industrial environmental challenges including temperature fluctuations, impact and unauthorized access. With its adaptability to both the industrial and networking environments, ProTek is nVent Hoffman's most versatile wall-mount networking solution.



ProTek
Double-Hinged
Fan Packages

ProTek cabinets are ideal for applications ranging from remote/decentralized networking and distribution, wireless access points, remote servers and data collection points, industrial controls and computers, HMI, enterprise systems, distributed controls, production monitoring systems, building automation and HVAC, security, audio-video systems, telecommunications and more. ProTek comes in a broad range of sizes, materials, configurations and options to suit the most extreme applications.



ProTek
Single-Door



ProTek
Double-Hinged Door

www.nVent.com/HOFFMAN

North America

Minneapolis, MN
Tel: +1.763.421.2240
Solon, OH
Tel: 1.800.497.4304
Mexico, D.F.
Tel: +52.55.5280.1449
Toronto, Canada
Tel: +1.416.289.2770

South America

Sao Paulo, Brazil
Tel: +55.11.5184.2100
Boitura, Brazil
Tel: +55.15.3363.9148

Europe

Andrézieux, France
Tel: +33.4.77.36.54.32
Straubenhardt, Germany
Tel: +49.7082.794.0
Dzierzoniow, Poland
Tel: +48.74.64.63.900
Lainate, Italy
Tel: +39.02. 2.7141

Middle East & India

Dubai, United Arab Emirates
Tel: +971.4.378.1700
Bangalore, India
Tel: +91.80.6715.2001

Asia

Shanghai, P.R. China
Tel: +86.21.2412.6943
Singapore
Tel: +65.6768.5800
Shin-Yokohama, Japan
Tel: +81.45.476.0271
Seoul, Korea
Tel: +82.2.2129.7755
Qingdao
Tel: +86.532.8771.6101



Our powerful portfolio of brands:

nVent.com

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

©2018 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

SEL00060_1803